





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	EC 0G3C 0005 05	05FEB05	BSV	JRO
			C1	REVISED PER ECO-09-020689	27AUG09	KK	AEC



- 1 HOUSING MATERIAL : GLASS FILLED, FLAME RETARDANT POLYESTER, COLOR-BLACK.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH : DUPLEX PLATED 0.00076 [.000030] GOLD ON CONTACT AREA, .00381-.00762 [.000150-.000300] BRIGHT TIN-LEAD ON SOLDER TINES, ALL OVER 0.00127 [.000050] MIN. NICKEL.
- 4 MOLDED IN ARROW DESIGNATES THE MATING FACE OF THE CONNECTOR.
- 5 DIMENSIONS PERTAIN TO CAVITY CENTERLINES.
- 6 POINT OF MEASUREMENT FOR PLATING THICKNESS OF CONTACT AREA.
- 7 DATE CODE AND PART NUMBER MARKED IN APPROXIMATE LOCATION SHOWN.
- 8 CONTACT FINISH : DUPLEX PLATED 0.00076 [.000030] GOLD ON CONTACT AREA, .00381-.00762 [.000150-.000300] MATTE TIN ON SOLDER LEADS, ALL OVER 1.27 [.000050] MIN. NICKEL.
- 9 ROHS 2002 /95/EC COMPLIANT
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

10	8	2, 6, 7, 9 THRU 14	35.56 [1.400]	38.10 [1.500]	15	9 5-146769-2
	8	2 THRU 7, 9 THRU 14	35.56 [1.400]	38.10 [1.500]	15	9 5-146769-1
10	3	2, 6, 7, 9 THRU 14	35.56 [1.400]	38.10 [1.500]	15	146769-2
	3	2 THRU 7, 9 THRU 14	35.56 [1.400]	38.10 [1.500]	15	146769-1
	FINISH	POSN NUMBERS OMITTED	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN E. BRANDBERG 30-AUG-96 CHK B. STAUCH 30-AUG-96 APVD B. STAUCH 30-AUG-96		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMPMODU MOD II, RECPT ASSY, HORIZONTAL, 2.54[.100] CL, 1 ROW, CLOSED ENTRY, SPOC, 0.00076 [.000030] GOLD DUPLEX, END STACK	SIZE A2	CAGE CODE 00779	DRAWING NO C-146769	RESTRICTED TO —		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -							PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	
MATERIAL 		FINISH 							CUSTOMER DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146769-1](#)