







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-	C		REVISED PER ECO 13-001843.	08FEB2013	MGM CT



SINGLE POLARIZATION



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

1. DWV RATING 875 VAC @ SEA LEVEL
2. WIRE SIZE: 24 AWG MAX
3. WORKING TEMPERATURE: -55°C ~ +125°C

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK

5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

6 PART IS MARKED WITH TE PART NUMBER, CHINA, DATE CODE AND LOT I.D.

7 ALL TOLERANCES TO BE ±0.20 MM UNLESS NOTED.

CHROMIUM-BLACK	DOUBLE	SOLDERING	10	11	33.45	ø12	ø14.9	2	2101550-2
CHROMIUM-BLACK	SINGLE	SOLDERING	10	11	33.45	ø12	ø14.9	2	2101550-1
FINISH	POLARIZATION	TERMINATION	Q	S	L	d	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.C THOMAS 21AUG2009	TE Connectivity				
DIMENSIONS: mm			CHK R. GROSS 21AUG2009					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD R. GROSS 21AUG2009	NAME				
0 PLC ± -			PRODUCT SPEC	CIRCULAR HD PLUG WITH PINS, SOLDER CUP 7 POS.				
1 PLC ± -			108-127005	-				
2 PLC ± 0.20			APPLICATION SPEC	-				
3 PLC ± -			-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
4 PLC ± -			WEIGHT	A2	00779	C=2101550	-	
ANGLES ± 3°			CUSTOMER DRAWING	SCALE	NTS	SHEET	1 OF 1	REV
FINISH								C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2101550-2](#)