


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		L2	REVISED PER ECO-15-011938	24AUG2015	NK	MM



D




- 7 0.00254-0.00508 [.000100-.000200] MATTE TIN OVER 0.00127 [.000050] MIN NICKEL ENTIRE POST.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 9 OBSOLETE

- 1 -Y- SHALL BE THE INTERSECTION OF THE POST AND THE HOUSING.
- 2 THE NOTED DIMENSION APPLIES FROM THE BASIC DIMENSION (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED.
- 3 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD OVER 0.00127 [.000050] MIN NICKEL ENTIRE POST.
- 4 PACKAGED IN TAPE AND REEL PER EIA-481 SPECIFICATIONS. SEE TABLE FOR TAPE WIDTH.
- 5 HOUSING: LCP, COLOR-BLACK. POST: COPPER ALLOY. PICK AND PLACE CAP: PPA, COLOR-BLACK.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.

C



B



RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

8 SUPERSEDED BY 5-147292-7

△ ₆	△ ₇	56mm	35.56 [1.400]	14	37.69 [1.484]	30	6-147292-4	
△ ₆	△ ₇	44mm	30.48 [1.200]	12	32.61 [1.284]	26	6-147292-3	
△ ₆	△ ₇	32mm	17.78 [.700]	7	19.91 [.784]	16	6-147292-2	
	△ ₇	24mm	12.70 [.500]	5	14.83 [.584]	12	6-147292-1	
	△ ₉	56mm	33.02 [1.300]	13	35.15 [1.384]	28	6-147292-0	
△ ₆	△ ₇	44mm	25.14 [.900]	9	24.99 [.984]	20	5-147292-9	
△ ₆	△ ₇	44mm	25.4 [1.000]	10	27.53 [1.084]	22	5-147292-8	
	△ ₇	44mm	27.94 [1.100]	11	30.07 [1.184]	24	5-147292-7	
	△ ₇	24mm	7.62 [.300]	3	9.75 [.384]	8	5-147292-6	
	△ ₆	32mm	20.32 [.800]	8	22.45 [.884]	18	5-147292-5	
	△ ₇	24mm	5.08 [.200]	2	72.14 [.284]	6	5-147292-4	
	△ ₇	24mm	2.54 [.100]	1	4.67 [.184]	4	5-147292-3	
	△ ₇	24mm	10.16 [.400]	4	12.29 [.484]	10	5-147292-2	
	△ ₇	32mm	15.24 [.600]	6	17.37 [.684]	14	5-147292-1	
	△ ₉	56mm	35.56 [1.400]	14	37.69 [1.484]	30	147292-8	
	2-7	△ ₃	44mm	27.94 [1.100]	11	30.07 [1.184]	24	147292-7
	△ ₉	△ ₃	24mm	7.62 [.300]	3	9.75 [.384]	8	147292-6
△ ₉	△ ₃	32mm	17.78 [.700]	7	19.91 [.784]	16	147292-5	
△ ₉	△ ₃	24mm	5.08 [.200]	2	72.14 [.284]	6	147292-4	
	△ ₃	24mm	2.54 [.100]	1	4.67 [.184]	4	147292-3	
	△ ₃	24mm	10.16 [.400]	4	12.29 [.484]	10	147292-2	
	△ ₈	△ ₃	32mm	15.24 [.600]	6	17.37 [.684]	14	147292-1
	PLATING	TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER	27MAR99	 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK J.GESFORD	27MAR99						
		APVD J.GESFORD	27MAR99	NAME SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, D/R, .100 X.100 C/L, .025 SQ POST, W/PICK AND PLACE CAP					
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± -							
MATERIAL 		FINISH SEE TABLE		APPLICATION SPEC —		SIZE A2	CAGE CODE —	DRAWING NO C=147292	RESTRICTED TO —
		WEIGHT —		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV L2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147292-3](#)