






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REV PER ECO 18-010457	7-24-18	CT	CJ
F		REVISED PER ECO-19-004671	26MAR2019	DCB	RL





DETAIL T
SCALE 20:1

- ⚠ MATERIAL: HOUSINGS; LCP, COLOR-NATURAL
CONTACT; BERYLLIUM COPPER
SOLDER BALL; SEE TABLE
TAPE, FILM; KAPTON WITH SILICON ADHESIVE
- ⚠ FINISH: CONTACT; GOLD (SEE TABLE) ON MATING AREA OVER
NICKEL ON ENTIRE CONTACT.



DETAIL X
SCALE 16:1



PCB LAYOUT (CONNECTOR SIDE)
SCALE 8:1

SUPERSEDED BY 2102080-4	2102079-4	12	0.76µm	8	LEAD FREE PER SAC405	2102080-8
SUPERSEDED BY 2102080-3	2102079-3	12	0.76µm	8	TIN LEAD	2102080-7
SUPERSEDED BY 2102080-2	2102079-4	10	0.76µm	6	LEAD FREE PER SAC405	2102080-6
SUPERSEDED BY 2102080-1	2102079-3	10	0.76µm	6	TIN LEAD	2102080-5
	2102079-2	12	1.27µm	8	LEAD FREE PER SAC405	2102080-4
	2102079-1	12	1.27µm	8	TIN LEAD	2102080-3
	2102079-2	10	1.27µm	6	LEAD FREE PER SAC405	2102080-2
	2102079-1	10	1.27µm	6	TIN LEAD	2102080-1
MATING PART NUMBER	MATED STACK HEIGHT (mm)	GOLD PLATING THICKNESS	H MAX REF	SOLDER BALL MATERIAL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. DOWDY 23JUL2009	TE Connectivity			
DIMENSIONS:		CHK K. DOWHOWER 23JUL2009	NAME			
mm		APVD K. DOWHOWER 23JUL2009	ASSEMBLY, SOCKET, 60 POSITION, MEZALOK STACKING CONNECTOR			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE			
0 PLC ±		108-2411	CAGE CODE			
1 PLC ±0.13		APPLICATION SPEC	DRAWING NO			
2 PLC ±		114-13279	RESTRICTED TO			
3 PLC ±		WEIGHT	A100779C=2102080			
4 PLC ±		CUSTOMER DRAWING	SCALE 8:1			
ANGLES			SHEET 1 OF 1			
FINISH			REV F			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2102080-6](#)