





LOC		DIST		REVISIONS					
GP	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			C	REV PER EC 09-028503			30DEC09	RG	DO




SCALE 5:1

- 1 MATERIAL: BRASS
2 MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY
3 FINISH: CONTACT MATING AREA .38μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN. Ni
4 FINISH: CONTACT MATING AREA 1.27μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN Ni
5 CONTACT SHOWN W/O CARRIER, OR HIDDEN LINES, FOR CLARITY
6 CUT OFF TO BE .13 MAX
7 INSULATION DIAMETER : 2.0-3.1 mm
8 WIRE DIAMETER: 16-20 AWG
10 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
11 FINISH: ENTIRE CONTACT 1.27μm MIN Au;
UNDERPLATE OVERALL 1.27μm MIN Ni

SCALE 12:1



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

			11.4	1-1489128-6
			9.8	1-1489128-5
			11.4	1-1489128-4
			9.8	1-1489128-3
	-		11.4	1-1489128-0
	-		9.8	1489128-9
	-		11.4	1489128-8
	-		9.8	1489128-7
	-		11.4	1489128-3
	-		9.8	1489128-2
MATERIAL	LOOSE PIECE	FINISH	DIM "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM	15 MAY 02	Tyco Electronics Corporation Middletown, Pa 17057	
DIMENSIONS: mm		CHK -	APVD -	NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ± -		108-1998	
		1 PLC ± -		APPLICATION SPEC	
2 PLC ± -		114-13067		SIZE	
3 PLC ± -		WEIGHT		CAGE CODE	
4 PLC ± -		CUSTOMER DRAWING		DRAWING NO	
ANGLES		SCALE 4:1		RESTRICTED TO	
FINISH		SHEET 1 OF 1		REV C	
1 2		3 4		1489128	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1489128-2](#)