




© 2020 TE Connectivity. All Rights Reserved.

1. MATERIAL:
BODY: ALUMINUM PER ASTM B317
INSERT: BRASS PER ASTM B36
2. FINISH:
BODY: .000600 MIN MATTE TIN PER ASTM B545
OVER .000060 MIN NICKEL PER ASTM B733.
INSERT: .000150 MIN MATTE NICKEL PER QQ-N-290
3. PTFE DRY LUBRICANT 360 DEGREE ON OUTER DIAMETER
OF CRIMP BARREL IN ZONE SHOWN.
4. WIRE INSULATION RANGE: .590-.683.
5. SEE TE CONNECTIVITY APPLICATION SPEC. 114-32098
FOR APPLICATION REQUIREMENTS.
6. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-32087
FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 3
FOR WIRE STRIPPING DETAIL.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REV PER ECO 19-019314	2-27-20	CT	PD



SCALE 1:1



2102575-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN 23AUG2012	TE Connectivity		
DIMENSIONS: INCHES		CHK DEBOCK, KIM 28NOV2012			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DEBOCK, KIM 28NOV2012	NAME ASSEMBLY, ALUMINUM TERMINAL, STRAIGHT, SINGLE HOLE, 4/0		
0 PLC ±.1 1 PLC ±.01 2 PLC ±.005 3 PLC ±.0005 4 PLC ±.0005 ANGLES ±1°		PRODUCT SPEC -	SIZE A200779	CAGE CODE C-2102575	RESTRICTED TO
MATERIAL SEE CALL-OUT material_2		FINISH SEE CALL-OUT finish_spec_2	WEIGHT -	SCALE 2:1	SHEET 1 OF 1
		CUSTOMER DRAWING	REV C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2102575-1](#)