




4		3		2		1					
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20							
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.							
NOTES: ⚠ MATERIALS AND FINISH HOUSING: PA 6-6, UL 94-V0, COLOR GRAY. CLAMP: BRASS, NICKEL PLATED. TERMINAL: BRASS, TIN PLATED. CLAMPING SCREW: M3, BRASS, NICKEL PLATED. 2. MECHANICAL WIRE STRIPPING LENGTH : 5.0-6.0 mm MIN. PC BOARD HOLES DIAMETER : 1.1 mm MAX. PC BOARD THICKNESS : 2.4 mm RECOMMENDED TIGHTENING TORQUE FOR SCREW: 0.5 Nm. 3. ELECTRICAL WIRE SIZE RANGE : 16-30 AWG. MAX. VOLTAGE : 300 V MAX CURRENT : 13.5 A CONTACT RESISTANCE : <15 m Ohm INSULATION RESISTANCE : >1000 M Ohm (500V DC) 4. OPERATING TEMPERATURE RANGE: -40°C TO +110°C 5. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING. 6. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE NO E60677. 7. PACKED IN TRAY. ⚠ NOT CUMULATIVE TOLERANCE. ⚠ PHIL-SLOT HEAD SCREW: M3, BRASS, NICKEL PLATED.						REVISIONS					
						P	LTR	DESCRIPTION	DATE	DWN	APVD
							-	SEE SHEET 1	-	-	-
						TE Connectivity					
TB, PCB MOUNT, SIDE WIRE ENTRY, STACK W/INTERLOCK, 5.00mm PITCH											
SIZE						CAGE CODE	DRAWING NO				
A200779						C=1546216	RESTRICTED TO				
CUSTOMER DRAWING						SCALE	4:1				
						SHEET	2 OF 2				
						REV	B1				

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1546216-2](#)