

PHYSICAL PROPERTIES:  
HOUSING MATERIAL: THERMOPLASTIC, PC  
FLAMABILITY: UL94V-0  
COLOR: BLACK


TERMINAL:  
TERMINALS: BRASS, TIN PLATED  
SCREWS: 6-32 STEEL, NICKEL PLATED

MECHANICAL:  
PITCH: .437  
WIRE RANGE: 14-22 AWG  
RECOMMENDED TIGHTENING TORQUE: 12IN-LB



ELECTRICAL PROPERTIES:  
MAX CURRENT: 25A  
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:  
OPERATING TEMP: -40°C TO 120°C

- 1 SEE FIGURE.
- 2 PRELIMINARY PART NUMBER.
- 3 STAINLESS STEEL SCREWS.
- 4 WHITE INK STAMP.
- 5 TE CONNECTIVITY LOGO LOCATED APPROXIMATE AREA.




	5.646	5.992	12	4-1546670-2
	9.142	9.488	20	2-1546670-0
	8.705	9.051	19	1-1546670-9
2	8.268	8.614	18	3-1546670-0
	8.268	8.614	18	1-1546670-8
	7.831	8.177	17	1-1546670-7
	7.394	7.740	16	1-1546670-6
	6.957	7.303	15	1-1546670-5
	6.520	6.866	14	1-1546670-4
	6.083	6.429	13	1-1546670-3
	5.646	5.992	12	1-1546670-2
	5.209	5.555	11	1-1546670-1
4	4.772	5.118	10	4-1546670-3
2	4.772	5.118	10	3-1546670-8
	4.772	5.118	10	1-1546670-0
2	4.335	4.681	9	3-1546670-5
2	4.335	4.681	9	3-1546670-2
	4.335	4.681	9	1546670-9
1	3.898	4.244	8	4-1546670-1
3	3.898	4.244	8	3-1546670-6
2	3.898	4.244	8	3-1546670-4
2	3.898	4.244	8	3-1546670-3
	3.898	4.244	8	1546670-8
	3.461	3.807	7	1546670-7
1	3.024	3.370	6	3-1546670-1
	3.024	3.370	6	1546670-6
1	2.587	2.933	5	2-1546670-8
1	2.587	2.933	5	2-1546670-7
	2.587	2.933	5	1546670-5
2	2.496	2.933	4	3-1546670-9
1	2.150	2.496	4	2-1546670-9
	2.150	2.496	4	1546670-4
	1.713	2.059	3	1546670-3
	1.276	1.622	2	1546670-2
	DIM B	DIM A	NO OF POS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHEGEL	4/4/03	 TE Connectivity							
		CHK C RICHARD	4/4/03								
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD	4/4/03	NAME					
		0 PLC ± -		PRODUCT SPEC		DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING					
		1 PLC ± -		—							
		2 PLC ± .01		APPLICATION SPEC							
		3 PLC ± .005		—							
4 PLC ± -		ANGLES ± 3°				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL —		FINISH —		WEIGHT —		A2	00779	C-1546670	—		
CUSTOMER DRAWING						SCALE	NTS	SHEET	1 of 3	REV	K18

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		—	SEE SHEET 1	—	—	—

DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5




JUMPER QTY 2





2-1546670-7

DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5





.250  
TYP



2-1546670-8


JUMPER, QTY 1




3-1546670-2

DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 9



DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 9



DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5




SINGLE SIDED, SINGLE HOLE  
QC TAB, QTY 2





2-1546670-9

SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 6





.250  
TYP



3-1546670-1

DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.


JUMPER, QTY 2




3-1546670-3

DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 6



DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 4



SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 18





.250  
TYP





3-1546670-0

DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.



3-1546670-4

11.764	12.110	26	2-1546670-6
11.327	11.673	25	2-1546670-5
10.90	11.236	24	2-1546670-4
10.453	10.799	23	2-1546670-3
10.016	10.362	22	2-1546670-2
9.579	9.925	21	2-1546670-1
9.142	9.488	20	3-1546670-7
DIM B	DIM A	NO OF POS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	S SCHEGEL		4/4/03		 TE Connectivity								
DIMENSIONS: INCHES				CHK	C RICHARD		4/4/03										
				TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD	C RICHARD		4/4/03		NAME  DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING				
								PRODUCT SPEC									
								APPLICATION SPEC									
MATERIAL  —				FINISH  —				WEIGHT  —		SIZE  A2		CAGE CODE  00779		DRAWING NO  C=1546670		RESTRICTED TO  —	
CUSTOMER DRAWING										SCALE  NTS		SHEET  2 of 3		REV  K18			

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D



DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 9.

JUMPER, QTY 1



3-1546670-5


DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 9




SINGLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 10

SINGLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 10

JUMPER, QTY 4




4-1546670-3




SINGLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 10


C





3-1546670-7



B




3-1546670-8




3-1546670-9

A



4-1546670-1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S	SCHEGEL	4/4/03			TE Connectivity	
DIMENSIONS: INCHES		CHK	C	RICHARD	4/4/03			NAME	
		APVD	C	RICHARD	4/4/03	PRODUCT SPEC		DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING	
		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		WEIGHT		A2		00779	C=1546670	-	
FINISH		CUSTOMER DRAWING		SCALE		NTS	SHEET	3 OF 3	REV
									K18

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1546670-2](#)