



LOC		DIST		REVISIONS					
FT		0		DESCRIPTION			DATE	DWN	APVD
		P	LTR						
			B1	REVISED PER ECO-10-009455			06MAY2010	HMR	CR





1. ELECTRICAL RATINGS: 300V, 20A
WIRE RANGE: 12-22 AWG
RECOMMENDED TIGHTENING TORQUE: 10 IN LBS
OPERATING TEMPERATURE: 105° MAX

△ TYCO ELECTRONICS LOGO LOCATED IN APPROXIMATE AREA SHOWN

6-32 SEMS SCREW, CAPTIVATED,
STEEL, ZINC PLATED CLEAR CHROMATE



HOUSING
NYLON, BLACK,
UL 94 V-0 RATED



RECOMMENDED PC BOARD LAYOUT

4.875	5.275	16	1-1546734-6
4.550	4.950	15	1-1546734-5
4.225	4.625	14	1-1546734-4
3.900	4.300	13	1-1546734-3
3.575	3.975	12	1-1546734-2
3.250	3.650	11	1-1546734-1
2.925	3.325	10	1-1546734-0
2.600	3.000	9	1546734-9
2.275	2.675	8	1546734-8
1.950	2.350	7	1546734-7
1.625	2.025	6	1546734-6
1.300	1.700	5	1546734-5
.975	1.375	4	1546734-4
.650	1.050	3	1546734-3
.325	.725	2	1546734-2
M	L	NO OF POSN	PART NUMBER

TYCO ELECTRONICS IS A REGISTERED TRADEMARK OF TYCO ELECTRONICS CORPORATION. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION. THIS DRAWING IS UNPUBLISHED.		DWN S. WELDON 11SEP2003	Tyco Electronics Harrisburg, PA 17105-3608	
CHK S. YODER 11SEP2003		NAME DUAL BARRIER STRIP ASSEMBLY, .325 PITCH, PCB MOUNT, HIGH RISE	RESTRICTED TO	
APVD S. YODER 11SEP2003		PRODUCT SPEC	SIZE A1	
DIMENSIONS: INCHES		APPLICATION SPEC	CAGE CODE 00779	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.1 1 PLC ±0.1 2 PLC ±0.02 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±.1 FINISH		WEIGHT	DRAWING NO C=1546734	
MATERIAL		CUSTOMER DRAWING	SCALE 4:1	
			SHEET 1	
			OF 1	
			REV B1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1546734-4](#)