



LOC	DIST	REVISONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD

CENTER
OF GRAVITY

3.81
CENTER OF
GRAVITY



I	MATERIALS AND FINISH: - HOUSING: LCP, COLOR: NATURAL - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni	B	REVISED PER ECR
		C	REVISED PER ECR

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS).

3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.

18AWG	MAX	INSULATION	OD:	2.20
20AWG	MAX	INSULATION	OD:	1.90
22AWG	MAX	INSULATION	OD:	1.70
24AWG	MAX	INSULATION	OD:	1.45





4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION, EXCEPT 1 POSITION CONNECTOR.

5 WIRE SIZE MARKING IN APPROXIMATE LOCATION SHOWN.

△₆ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

 COLOR CODE MARKING, STRAIGHT LINE.


8 | POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




RED	17.70	24 AWG	4	3-2106431-4
	13.70	24 AWG	3	3-2106431-3
	9.70	24 AWG	2	3-2106431-2
	5.70	24 AWG	1	 3-2106431-1
GREEN	17.70	22 AWG	4	2-2106431-4
	13.70	22 AWG	3	2-2106431-3
	9.70	22 AWG	2	2-2106431-2
	5.70	22 AWG	1	 2-2106431-1
BLUE	17.70	20 AWG	4	1-2106431-4
	13.70	20 AWG	3	1-2106431-3
	9.70	20 AWG	2	1-2106431-2
	5.70	20 AWG	1	 1-2106431-1
YELLOW	17.70	18 AWG	4	2106431-4
	13.70	18 AWG	3	2106431-3
	9.70	18 AWG	2	2106431-2
	5.70	18 AWG	1	 2106431-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DAILY CHK J DYER 09DEC2008 09DEC2008		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266	
MATERIAL		WEIGHT		SIZE	CAGE CODE
		-		A2	00779
		-		C=2106431	
Customer Drawing				SCALE	8.1
				SHEET	1 of 3
				REV	C


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




I POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1



2 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09DEC2008 C DAILY CHK J DYER 09DEC2008 APVD -		 TE Connectivity						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. ±.		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266		NAME ASSEMBLY, IDC SSL CONNECTOR, SMT, PASS THRU				
						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL - material-2		FINISH - finish_spec-2		WEIGHT -		A200779		©-2106431		-
Customer Drawing						SCALE	8:1	SHEET	1 OF 3	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2106431-2](#)