










P.C.B. HOLE LAYOUT

TOLERANCE $\pm .003$

1. INSULATOR MATERIAL - THERMOPLASTIC POLYESTER, PCT, BLACK, UL94 V-O
2. MACHINED CONTACT - BECU, PLATED WITH 80-200 μ ".
TIN (LEAD FREE) OVER 75-100 μ " COPPER.
3. SLEEVE - COPPER, PLATED WITH 180-340 μ "
THK TIN (LEAD FREE) OVER 75-125 MIN NICKEL.
4. MACHINED CONTACT - BECU, PLATED WITH 25 μ " MIN.
GOLD OVER 30-100 μ " NICKEL.
5. ELECTRICAL:
CONTACT RESISTANCE: 10 MILLIOHMS MAX
CONTACT RATING: 3 AMPS
CAPACITANCE: 1.0 pF PER MIL-STD-202, METHOD 305
INSULATION RESISTANCE: 5000 OHMS MIN @ 500 VDC PER
MIL-STD-1344, METHOD 3003.1
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS (RMS) PER
MIL-STD-1344, METHOD 3001.1
6. MECHANICAL:
INSERTION FORCE: 134 GRAMS AVG
WITHDRAWAL FORCE: 63 GRAMS AVG
"ACCEPTS IC PIN - .009"X.015" THROUGH .011"X.020", OR
.016" TO .021" DIAMETER, .150/.105 LONG"
7. ENVIRONMENTAL:
OPERATING TEMPERATURE: -55°C TO -105°C
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.KRAYBILL	07NOV03	 TE Connectivity				
DIMENSIONS:		CHK K.WRIGHT	-	NAME OPEN FRAME DIP, PREMIUM (MACHINE CONTACT), LEAD FREE (REF AUGAT 800 SERIES)				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.WRIGHT	-					
INCHES		PRODUCT SPEC	-					
		APPLICATION SPEC	-					
			-					
MATERIAL	FINISH	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-	-	-	-	A1	00779	C=1571586	-	
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 2	REV B

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				-				-			
COPYRIGHT - By -				ALL RIGHTS RESERVED.											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571586-2](#)