





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD



2 POSITION
SHOWN AS SHIPPED



- | | | | | |
|---|--|--|--|--|
| △ | MATERIALS AND FINISH: | | | |
| | - HOUSING: LCP, COLOR: NATURAL | | | |
| | - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni | | | |

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.


18 AWG	MAX	INSULATION	OD	2.20
20 AWG	MAX	INSULATION	OD	1.90
22 AWG	MAX	INSULATION	OD	1.70
24 AWG	MAX	INSULATION	OD	1.45

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

5 WIRE SIZE MARKING IN APPROXIMATE LOCAITON SHOWN.

 COLOR CODE MARKING, STRAIGHT LINE.

△ 7 ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




2 POSITION
SHOWN CLOSED
SCALE 8:1


RED	17.70	24 AWG	4	3-2106751-4
	13.70	24 AWG	3	3-2106751-3
	9.70	24 AWG	2	3-2106751-2
	5.70	24 AWG	1	 3-2106751-1
GREEN	17.70	22 AWG	4	2-2106751-4
	13.70	22 AWG	3	2-2106751-3
	9.70	22 AWG	2	2-2106751-2
	5.70	22 AWG	1	 2-2106751-1
BLUE	17.70	20 AWG	4	1-2106751-4
	13.70	20 AWG	3	1-2106751-3
	9.70	20 AWG	2	1-2106751-2
	5.70	20 AWG	1	 1-2106751-1
YELLOW	17.70	18 AWG	4	2106751-4
	13.70	18 AWG	3	2106751-3
	9.70	18 AWG	2	2106751-2
	5.70	18 AWG	1	 2106751-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCOY CHR 26AUG2009 O. OSAGIE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU	
		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266		SIZE A2	
MATERIAL  -  -		WEIGHT -		CAGE CODE 00779	
		Customer Drawing		DRAWING NO C-2106751	
				RESTRICTED TO -	
				SCALE 8:1 SHEET 1 OF 3 REV C	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




1 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1






2 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCYOC	TE Connectivity			
DIMENSIONS: mm		CHK 26AUG2009 O. OSAGIE				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME			
0 PLC ±		PRODUCT SPEC	ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU			
1 PLC ±0.5		108-2404				
2 PLC ±0.13		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO			
3 PLC ±		114-13266	A200779C-2106751			
4 PLC ±		WEIGHT -				
MATERIAL -		Customer Drawing	RESTRICTED TO			
finish_spec_2		SCALE 8:1	SHEET 1 OF 3			
			REV C			



SECTION Y-Y

2106751-2 SHOWN IN POCKET TAPE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2106751-2](#)