





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD




2 POSITION
SHOWN AS SHIPPED



FOR 2, 3 AND
4 POSITIONS



FOR 1 POSITION
ONLY



- | | | |
|---|--|--|
| △ | MATERIALS AND FINISH: | |
| | - HOUSING: LCP, COLOR: NATURAL | |
| | - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni | |

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)


3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.
- | | | | | |
|--------|-----|------------|----|------|
| 18 AWG | MAX | INSULATION | OD | 2.20 |
| 20 AWG | MAX | INSULATION | OD | 1.90 |
| 22 AWG | MAX | INSULATION | OD | 1.70 |
| 24 AWG | MAX | INSULATION | OD | 1.45 |

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

5 WIRE SIZE MARKING IN APPROXIMATE LOCAITON SHOWN.

 COLOR CODE MARKING, STRAIGHT LINE.

7 ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




2 POSITION
SHOWN CLOSED
SCALE 8:1


RED	17.70	24 AWG	4	3-2106751-4
	13.70	24 AWG	3	3-2106751-3
	9.70	24 AWG	2	3-2106751-2
	5.70	24 AWG	1	 3-2106751-1
GREEN	17.70	22 AWG	4	2-2106751-4
	13.70	22 AWG	3	2-2106751-3
	9.70	22 AWG	2	2-2106751-2
	5.70	22 AWG	1	 2-2106751-1
BLUE	17.70	20 AWG	4	1-2106751-4
	13.70	20 AWG	3	1-2106751-3
	9.70	20 AWG	2	1-2106751-2
	5.70	20 AWG	1	 1-2106751-1
YELLOW	17.70	18 AWG	4	2106751-4
	13.70	18 AWG	3	2106751-3
	9.70	18 AWG	2	2106751-2
	5.70	18 AWG	1	 2106751-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCOY CHK 26AUG2009 O. OSAGIE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.5 1 PLC ±0.13 2 PLC ±.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU	
		PRODUCT SPEC 108-2404		SIZE A2	
MATERIAL  - 		APPLICATION SPEC 114-13266		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-2106751	
Customer Drawing		SCALE 8.1		SHEET 1 OF 3 REV C	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




1 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1






2 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCYOC	TE Connectivity			
DIMENSIONS:		CHK 26AUG2009 O. OSAGIE				
mm		APVD -	NAME			
		PRODUCT SPEC	ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
material_2		-	A200779	C-2106751	-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		Customer Drawing				
0 PLC ±		SCALE 8:1				
1 PLC ±0.5		SHEET 1 OF 3				
2 PLC ±0.13		REV C				
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						
-						



SECTION Y-Y

2106751-2 SHOWN IN POCKET TAPE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2106751-3](#)