



D

C

B



A



KEY POSITION CHART			
NONE			
A	E		
B	F		
C	G		
D	H		


150X $\varnothing 0.39 \pm 0.05$
PLATED THRU HOLE

150X $\varnothing 0.48 \pm 0.013$
DRILL HOLE
 $\varnothing 0.10$



RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.0

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30 μ " SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.
3. CONNECTORS SUPPLIED WITH MOUNTING SCREW.



SCALE 4:1

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

H	2	8-2110105-1
G	2	7-2110105-1
F	2	6-2110105-1
E	2	5-2110105-1
D	2	4-2110105-1
C	2	3-2110105-1
B	2	2-2110105-1
A	2	1-2110105-1
NONE	2	2110105-1
KEY POSITION	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. K. SHOBER 14FEB2011	 TE Connectivity			
DIMENSIONS:		CHK D. DIXON 14FEB2011				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. DIXON 14FEB2011	NAME	IMPACT, 5 PAIR, DAUGHTERCARD 10 COLUMN, RIGHT GUIDED, SIGNAL MODULE, 0.39 EYELET		
	0 PLC ± 0.2	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	2 PLC ± 0.13	APPLICATION SPEC				
MATERIAL	4 PLC ± 0.13	WEIGHT	A100779C=2110105		-	
	FINISH SEE TABLE	CUSTOMER DRAWING	SCALE 6:1		SHEET 1 OF 1	
ANGLES					REV C2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2110105-1](#)