






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECO-15-003239	24MAR2015	AP	DD




- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µm SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
- 4 UNGUIDED RIGHT ANGLE MALE MATES TO
UNGUIDED RIGHT ANGLE RECEPTACLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	06APR2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY	06APR2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY	06APR2011	NAME	IMPACT, STD, RAM, 2 PAIR, 10 COLUMN, UNGUIDED DUAL END WALL SIGNAL MODULE, 0.39 EYELET
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC	-	SIZE	CAGE CODE DRAWING NO
MATERIAL	FINISH SEE TABLE	APPLICATION SPEC	-	RESTRICTED TO	-
	-	WEIGHT	-	A100779	©=2143014
Customer Drawing			SCALE	5:1	SHEET 1 OF 2 REV B1

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-



COPLANAR MATED SIGNAL PATHS



	5.50	2143014-6
	4.90	2143014-5
	5.50	2143014-3
	4.90	2143014-2
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	06APR2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY	06APR2011		
	mm	APVD J. EABY	06APR2011	NAME IMPACT, STD, RAM, 2 PAIR, 10 COLUMN, UNGUIDED DUAL END WALL SIGNAL MODULE, 0.39 EYELET	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
	0 PLC ±0.25		APPLICATION SPEC		
	1 PLC ±0.13		WEIGHT -		
MATERIAL		SEE TABLE		SIZE A100779C=2143014	
		Customer Drawing		RESTRICTED TO -	
				SCALE 5:1 SHEET 2 OF 2 REV B1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2143014-2](#)