






SIZE	B DIM	C DIM ±.0050	(L DIM)
09	.229	.3085	(.100)
15	.304	.3835	(.175)
25	.429	.5085	(.300)
37	.579	.6585	(.450)
51	.754	.8335	(.625)
65	.929	1.0085	(.800)

1. SHELL OPTIONS (TO BE SPECIFIED IN NANONICS PART NUMBER):
 METAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 (STANDARD) OR GOLD PLATED PER ASTM B488
 303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-2700
 INSULATOR MATERIAL FOR ALL METAL SHELLS IS LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138
 PLASTIC: LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138
 2. STANDARD 1.0 X 0.25mm MOUNTING AND JACKSCREW THREADS ARE SHOWN FOR REFERENCE ONLY AND MUST BE SPECIFIED IN THE NANONICS PART NUMBER WHEN REQUIRED. 1.2 X 0.25mm THREADS ALSO AVAILABLE.
 3. MOUNTING HARDWARE IS AVAILABLE WITH THIS CONFIGURATION (NOT SHOWN). HARDWARE MUST BE SPECIFIED IN THE NANONICS PART NUMBER. CONSULT TE CONNECTIVITY FOR DETAILS.
 4. LEADS ARE HH BRASS, TIN LEAD PLATED 60/40 COMPOSITION PER SAE-AMS-P-81728.
 5. LEAD ORGANIZER MATERIAL IS LIQUID CRYSTAL POLYMER PER ASTM D5138.
 6. THROUGH HOLE LEADS ARE EPOXY ENCAPSULATED WITHIN THE LEAD ORGANIZER.
 7. TERMINATION CODE: M6
 8. THIS DRAWING PREVIOUSLY IDENTIFIED AS NANONICS **N10138/250**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RYAN 15 JUN 00 CHK M. STORRY 15 JUN 00 APVD S. KAIN 15 JUN 00		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .010 3 PLC ± .005 4 PLC ± — ANGLES ± 1°		NAME RECEPTACLE ASSEMBLY, HORIZONTAL MOUNT, THROUGH HOLE, 2 TO 4 ROW, .050 SPACING, PLASTIC OR METAL	
MATERIAL		WEIGHT			
SEE NOTES		FINISH		SIZE A2	
				CAGE CODE OPJN9	
				DRAWING NO G-1589487	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 8:1	
				SHEET 1 of 2	
				REV T1	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RYAN 15 JUN 00		 TE Connectivity									
DIMENSIONS: INCHES		CHK M. STORRY 15 JUN 00											
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. KAIN 15 JUN 00		NAME RECEPTACLE ASSEMBLY, HORIZONTAL MOUNT, THROUGH HOLE, 2 TO 4 ROW, .050 SPACING, PLASTIC OR METAL								
	0 PLC ± -		PRODUCT SPEC										
	1 PLC ± -		—										
	2 PLC ± .010		APPLICATION SPEC										
	3 PLC ± .005		—										
MATERIAL	4 PLC ± -		WEIGHT		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO				
	ANGLES ± 1°		—		A2	0PJN9	C=1589487		—				
	FINISH		—										
SEE NOTES		SEE NOTES		CUSTOMER DRAWING				SCALE	8:1	SHEET	2 OF 2	REV	T1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1589487-3](#)