

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECO-14-003208	17MAR2014	NK	DR
	G3	REVISED PER ECO-18-002275	19FEB2018	RS	DR




- 1 WIRE SIZE IS #16-#14 AWG
- 2 SUPERSEDED BY 165171
- 3 OBSOLETE - NO REPLACEMENT
- 4 STAMP AMP 16-14* APPROX AS SHOWN
- 5 MAX RECOMMENDED OPERATING TEMPERATURE 105°C[221°F]
- 6 MATERIAL: BODY-COPPER PER ASTM B152 INSULATION-PVC
- 7 FINISH: BODY-TIN PLATE .00254[.000100] MIN EXT THK PER ASTM B454 INSULATION-COLOR-BLUE

2.921-4.318[.115-.170]	---	165171-12
2.921-4.826[.115-.190]	2-165171-03	165171
INSUL DIA RANGE. "A"	P/N ON TAPE	PART NO.

AMP WIRE RANGE	RA FILE E13288
16-14 AWG STRANDED	16-14 AWG STRANDED

1000	LOOSE PIECE	165171
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 31MAY07	STE TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		CHK T MICHIELUTTI 31MAY07				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI 31MAY07	NAME		
	0 PLC ± -		PRODUCT SPEC	UL486 A-B		
	1 PLC ± -		APPLICATION SPEC	114-2161		
	2 PLC ± -		WEIGHT	-		
3 PLC ± 0.203[.008]			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -			A2	00779	C=165171	-
ANGLES ± 1°			CUSTOMER DRAWING			
FINISH			SCALE	SHEET	REV	
6		7	8:1	1 of 1	G3	



SECTION A-A

SECTION B-B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[165171](#)