

D

C

B


A

D


C

B


A




1. COMPONENTS
CAGE ASSEMBLY: NICKEL-SILVER ALLOY
EMI SPRING: COPPER ALLOY/NICKEL PLATE
LIGHT PIPE: CLEAR POLYCARBONATE
ORGANIZER: POLYESTER
2. REFERENCE APPLICATION SPECIFICATION 114-32023
FOR RECOMMENDED DRILL HOLE DIAMETER AND
PLATING THICKNESS
3. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
4. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
5. LIGHT PIPES ARE SHIPPED ASSEMBLED ON CAGE
6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 2.20 MIN
7. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
8. THESE HOLES ARE OPTIONAL WHEN THE REAR PINS ARE REMOVED.
9. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.



SCALE 2:1



SEE DETAIL C



DETAIL C
SCALE 6:1

DUAL	WITHOUT	2170739-2
DUAL	WITH	2170739-1
LIGHT PIPE OPTIONAL	REAR PINS OPTIONAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.25
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	±

SEE NOTES

DWN

BING LIU

04JUL2014

CHK

JASON YANG

04JUL2014

APVD

SEAN HAN

03NOV2016

PRODUCT SPEC

108-19428

APPLICATION SPEC

114-32023

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE CAGE ASSEMBLY
WITH LIGHT PIPES,
THRU BEZEL, 1X3, QSFP28

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2170739	-

SCALE	3:1	SHEET	1	OF	6	REV	A
-------	-----	-------	---	----	---	-----	---

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

D

D

C



C

B

B


A

A




SCALE 3:1
UNDIMENSIONED DIMENSION SAME AS 2170739-1

LIGHT PIPE



SCALE 3:1

1X3 CAGE ASSEMBLY



SINGLE	WITH	2170739-3
LIGHT PIPE	REAR PINS	PART NUMBER
OPTIONAL	OPTIONAL	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.25

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

SEE NOTES

material_2

DWN BING LIU 04JUL2014

CHK JASON YANG 04JUL2014

APVD SEAN HAN 03NOV2016

PRODUCT SPEC 108-19428

APPLICATION SPEC 114-32023

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME RECEPTACLE CAGE ASSEMBLY WITH LIGHT PIPES, THRU BEZEL, 1X3, QSFP28

SIZE A2

CAGE CODE 00779


DRAWING NO C-2170739


RESTRICTED TO -

SCALE 3:1

SHEET 2 OF 6

REV A





RECOMMENDED PCB LAYOUT
SINGLE TYPE
PCB TOLERANCE: ± 0.05
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 04JUL2014	TE Connectivity		
DIMENSIONS: mm		CHK JASON YANG 04JUL2014			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SEAN HAN 03NOV2016	NAME RECEPTACLE CAGE ASSEMBLY WITH LIGHT PIPES, THRU BEZEL, 1X3, QSFP28		
0 PLC $\pm$ -		PRODUCT SPEC	SIZE A200779		
1 PLC ± 0.25		APPLICATION SPEC	CAGE CODE C-2170739		
2 PLC ± 0.2		114-32023	DRAWING NO		
3 PLC $\pm$ -		WEIGHT	RESTRICTED TO		
4 PLC $\pm$ -		-	-		
ANGLES $\pm$ -		CUSTOMER DRAWING	SCALE 3:1 SHEET 4 OF 6 REV A		
FINISH					
SEE NOTES material_2		SEE NOTES finish_spec_2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170739-2](#)