




19.57 REF


57.43 REF

3. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.

5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.

 DATUM -A- IS TOP SURFACE OF THE HOST BOARD.

8 DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN



9.72 REF


$$8.90 \pm 0.10$$

9.70

2.05

66 —


125



2.20

5.00


0	WITH	2170752-7
1	WITH	2170752-6
0	WITHOUT	2170752-5
1	WITHOUT	2170752-4
2	WITH	2170752-2
2	WITHOUT	2170752-1
# REAR PINS	HEAT SINK OPEN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG	01APR2014			TE Connectivity	
		CWH SEAN HAN	30DEC2015				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
mm			APVD -	CAGE ASSEMBLY, QSFP28 1X1, THRU BEZEL WITH EMI GASKET			
			PRODUCT SPEC				
			108-19428				
			APPLICATION SPEC				
			114-32023				
MATERIAL	FINISH		WEIGHT	SIZE CAGE CODE DRAWING NO		RESTRICTED TO	
-	-		-	A 00779 ©=2170752		-	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 5	REV A


2170752-1 AS SHOWN

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			-	SEE SHEET 1		-	-	-

HEAT SINK OPEN OPTIONS




WITHOUT HEAT SINK OPEN
SCALE 4:1




WITH HEAT SINK OPEN
SCALE 4:1

OF REAR LEGS OPTIONS




(2.20) (5.00)

2 REAR LEGS VERSION
SCALE 4:1



7.38





1 REAR LEG VERSION
SCALE 4:1



0 REAR LEG VERSION
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014 CHK: SEAN HAN 30DEC2015 APVD: -	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023	NAME CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET
mm	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ± FINISH -			
MATERIAL	-	WEIGHT	-	RESTRICTED TO
-	-	Customer Drawing	SCALE 4:1	SHEET 2 OF 5 REV A

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG: JASON YANG 01APR2014	 TE Connectivity	
		CHK: SEAN HAN 30DEC2015		
DIMENSIONS:		APPROV: -	NAME	
mm			CAGE ASSEMBLY, QSFP28 1X1, THRU BEZEL WITH EMI GASKET	
		0 PLC ±0.25	PRODUCT SPEC	
		1 PLC ±0.25	108-19478	
		2 PLC ±0.20	-	
		3 PLC ±0.100	-	
		4 PLC ±	114-32023	
ANGLES			SIZE	
FINISH			CAGE CODE	
MATERIAL		WEIGHT	DRAWING NO	
			A100779C=2170752	
		Customer Drawing	RESTRICTED TO	
			SCALE 4:1	
			SHEET 3 OF 5	
			REV A	





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

D

C

B

A




C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity	
DIMENSIONS: mm		CHK: SEAN HAN 30DEC2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: -	NAME: CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET	
0 PLC ± 0.25		PRODUCT SPEC: 108-19428	SIZE: CAGE CODE: DRAWING NO: A100779C=2170752	
1 PLC ± 0.25		APPLICATION SPEC: 114-32023		
2 PLC ± 0.20		WEIGHT: -	RESTRICTED TO: -	
3 PLC ± 0.100		Customer Drawing		
4 PLC $\pm$			SCALE 4:1 SHEET 4 OF 5 REV A	
ANGLES FINISH				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170752-7](#)