





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
-	-		BA	NEW DRAWING		24APR2012	ST.P



FOR FURTHER INFORMATION SEE DATA SHEET FOR
3650 SERIES-LOW INDUCTANCE,HIGH FREQUENCY CHIP INDUCTOR



SERIES	A Max.	B Max.	C Max.	E	F	G	H	I	J
3654 1E	1.15	0.70	0.60	0.45	0.20	0.60	0.65	0.35	0.50



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.5

2 PLC ±0.2

3 PLC ±0.1

4 PLC ±0.0001

ANGLES ±

FINISH
-

DWN 24APR2012
RAGHAVENDRA K

CHK 24APR2012
ALLAN P

APVD 24APR2012
STEPHEN.P

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
0.001 GRAM

CUSTOMER DRAWING

TE Connectivity

NAME
-

CHIP INDUCTOR TYPE 3654 0201 SERIES

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=2176086

RESTRICTED TO
-

SCALE
32:1

SHEET
1

OF
1

REV
BA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2176086-4](#)