



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


OF REAR LEGS OPTION




PN: 2170773-1/2/3




BACK VIEW OF 2170773-1
SCALE 4:1




BACK VIEW OF 2170773-2
SCALE 4:1




BACK VIEW OF 2170773-3
SCALE 4:1




PN: 2170773-4/5/6



BACK VIEW OF 2170773-4
SCALE 4:1




BACK VIEW OF 2170773-5
SCALE 4:1





BACK VIEW OF 2170773-6
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 23SEP2013 CHK SEAN HAN 23SEP2013 APVD 23SEP2013		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ±		NAME CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER LIGHT PIPE	
		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023		SIZE CAGE CODE DRAWING NO A100779C=2170773	
MATERIAL		FINISH		RESTRICTED TO	
-		-		-	
CUSTOMER DRAWING				SCALE 2:1 SHEET 2 OF 7 REV A	


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	-	SEE SHEET 1	-	-	-




2170773-7 AS SHOWN
SCALE 4:1




2170773-7 BACK VIEW
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. JASON YANG 23SEP2013	 TE Connectivity		
		CHK. SEAN HAN 23SEP2013			
DIMENSIONS:		APVD. 23SEP2013	NAME	CAGE ASSEMBLY, OSFP28, THRU BEZEL WITH EMI SPRING FINGER LIGHT PIPE	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC			
	0 PLC ±0.25	108-19428	SIZE CAGE CODE DRAWING NO		
	1 PLC ±0.25	APPLICATION SPEC			
	2 PLC ±0.20	114-32023	RESTRICTED TO		
	3 PLC ±0.100	WEIGHT			
MATERIAL		CUSTOMER DRAWING	A100779C=2170773		
			SCALE 2:1	SHEET 3 OF 7	
				REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-







RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1

4805 (3/13)


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 2 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1




RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



DETAIL C
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 23SEP2013	TE Connectivity	
DIMENSIONS:		CHK: SEAN HAN 23SEP2013		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: JASON YANG 23SEP2013	NAME: CAGE ASSEMBLY, OSFP28, THRU BEZEL WITH EMI SPRING FINGER LIGHT PIPE	
Ø	0 PLC ±0.25	PRODUCT SPEC	SIZE: A100779C=2170773	
	1 PLC ±0.25	108-19428	CAGE CODE DRAWING NO	
	2 PLC ±0.25	APPLICATION SPEC	RESTRICTED TO	
	3 PLC ±0.20	114-32023	SCALE 2:1 SHEET 6 OF 7 REV A	
	4 PLC ±0.100	WEIGHT		
	ANGLES ±°	CUSTOMER DRAWING		
MATERIAL	FINISH			
-	-			
-	-			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL D
SCALE 12:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 23SEP2013	TE Connectivity	
		CHK SEAN HAN 23SEP2013		
DIMENSIONS:		APVD 23SEP2013	NAME CAGE ASSEMBLY, OSFP28, THRU BEZEL WITH EMI SPRING FINGER LIGHT PIPE	
mm		PRODUCT SPEC 108-19428		
		APPLICATION SPEC 114-32023	SIZE A100779	
		WEIGHT -		
MATERIAL -		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 2:1	SHEET 7	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170773-5](#)