





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
-	-		BA	NEW DRAWING		24APR2012	ST.P



FOR FURTHER INFORMATION SEE DATA SHEET FOR
3650 SERIES-LOW INDUCTANCE,HIGH FREQUENCY CHIP INDUCTOR



SERIES	A Max.	B Max.	C Max.	E	F	G	H	I	J
3654 1E	1.15	0.70	0.60	0.45	0.20	0.60	0.65	0.35	0.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.5
2 PLC ±0.2
3 PLC ±0.1
4 PLC ±0.0001
ANGLES ±-
FINISH -

0.001 GRAM

DWN 24APR2012
RAGHAVENDRA K
CHK 24APR2012
ALLAN P
APVD 24APR2012
STEPHEN.P
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT 0.001 GRAM

TE Connectivity

NAME -
CHIP INDUCTOR TYPE 3654 0201 SERIES
-
SIZE CAGE CODE DRAWING NO RESTRICTED TO
A3 00779 C=2176086 -

CUSTOMER DRAWING SCALE 32:1 SHEET 1 OF 1 REV BA

1470-19 (3/11)
Pro/ENGINEER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2176086-2](#)