






LOC		DIST		REVISIONS					
-		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					B	REVISED PER ECR-16-003314	18JUL2016	BW	GJ
					B1	REVISED PER ECR-18-002671	07NOV2018	BKW	GJ



POS.	DIM.A	DIM.B	DIM.C
1*5	33.70	27.50	31.30
1*4	27.70	21.50	25.30
1*3	21.70	15.50	19.30
1*2	15.70	9.50	13.30



1. MATERIAL:
LEVEL A:PA6 GLASS FILLED,COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF
NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION
DETAILED IN IEC 60335-1, SECTION 30 (GWT),UL 94V-0
LEVEL B:PBT GLASS FILLED,HOT WIRE IGNITION (HWI) VERSION ARE MOLDED IN
A RESIN THAT COMPLIES WITH TE HOT WIRE IGNITION TEST 109-32026
AND ARE RECOMMENDED FOR USE WITH HWI HOUSINGS THAT ALSO COMPLY,
UL 94V-0

2. MATERIAL MARK:
LEVEL A:GWT,LEVEL B:HWT









3. APPLICABLE CONTACT P/N
TAB CONTACT:1971238/1971780/82/84/86/88-*,2238067-*

4. MATING CONN, P/N
PLUG HSG:*-2232265-
TPA (LOCK PLATE):*-1971777-*



5. This product has not completed validation testing.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TOMMY WU	26MAR2013	 TE Connectivity			
		CHK	HAPYE WU	26MAR2013				
DIMENSIONS:		APVD	YUZHONG MAO	26MAR2013	NAME			
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			CAP HOUSING,FREE HANGING,SINGLE ROW			
		0 PLC ±			POWER TRIPLE LOCK			
		1 PLC ±0.35			-			
		2 PLC ±0.25			SIZE			
		3 PLC ±			CAGE CODE			
		4 PLC ±			DRAWING NO			
		ANGLES ±			A100779			
		FINISH			C=2232358			
MATERIAL		WEIGHT			RESTRICTED TO			
-		-			-			
		Customer Drawing			SCALE			
		-			SHEET 1 OF 2			
					REV B1			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	-	-	SEE SHEET 1	-	-	-





1*2 POSITIONS





KEYING FOR 1*2 POS.

1*3 POSITIONS





KEYING FOR 1*3 POS.

1*4 POSITIONS



KEYING FOR 1*4 POS.

1*5 POSITIONS



KEYING FOR 1*5 POS.

1*5	LEVEL A	DARK GREY	KEY A	5-2232358-7
		BROWN	KEY B	6-2232358-7
		GREEN	KEY C	7-2232358-7
		ORANGE	KEY D	8-2232358-7
1*4	LEVEL A	DARK GREY	KEY A	5-2232358-4
		BROWN	KEY B	6-2232358-4
		GREEN	KEY C	7-2232358-4
		ORANGE	KEY D	8-2232358-4
1*3	LEVEL B	BLACK	KEY A	1-2232358-3
		DARK GREY	KEY A	5-2232358-3
		BROWN	KEY B	6-2232358-3
		GREEN	KEY C	7-2232358-3
1*2	LEVEL A	ORANGE	KEY D	8-2232358-3
		DARK GREY	KEY A	5-2232358-2
		BROWN	KEY B	6-2232358-2
		GREEN	KEY C	7-2232358-2
POS.	MATERIAL	COLOR	KEY	P/N

SUPERSEDED BY POWER TRIPLE LOCK
PANEL MOUNT CAPS X-2232263-X

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY_WU	26MAR2013	TE Connectivity	
		CHK HAPYE_WU	26MAR2013		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±.035		CAP HOUSING, FREE HANGING, SINGLE ROW	
		2 PLC ±0.25		POWER TRIPLE LOCK	
		3 PLC ±.		-	
		4 PLC ±.		SIZE	
		ANGLES FINISH		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
-		-		A100779	
		Customer Drawing		RESTRICTED TO	
				SCALE	
				SHEET 2 OF 2	
				REV B1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2232358-4](#)