





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-19-013267	08JAN2020	WH	DZ




- 1 MATERIAL: PHOSPHOR BRONZE.
- 2 FINISH: PRE-TIN.
- 3 DESIGNED FOR USE IN HOUSINGS []-1969442-[[OR []-1744417-[].
- 4 CONTACTS COATED WITH ANTI-FRETTING LUBRICANT.
- 5 CONTACT IS RoHS COMPLIANT.
- 6 WIRE RANGE: 0.13~0.36mm2 [26-22 AWG] STRANDED.
7. INSULATION RANGE: 1.30~1.91
- 8 AFTER CRIMP DIMENSION
- 9 MEASURE LOCATION FOR 0.50mm MAX DIMENSION



SECTION A-A



SECTION B-B



SECTION C-C

2232905-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN OTTO CHEN 25JUN2015	TE Connectivity			
		CHK DANIEL 26JUN2015				
		APVD DANIEL 26JUN2015	NAME LOW INSERTION FORCE CONTACT EP 2.5, RECEPTACLE			
DIMENSIONS: mm		PRODUCT SPEC 108-2418	SIZE A2		CAGE CODE 00779	
		APPLICATION SPEC 114-13315	DRAWING NO C-2232905		RESTRICTED TO -	
MATERIAL 1 -		WEIGHT -	SCALE N/A		SHEET 1 OF 1	
		Customer Drawing			REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2232905-1 \(Mouser Reel\)](#)