








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REDRAWN IN CREO	05APR2019	RS	JO



- 1 0.00076[.000030] GOLD AT POINT OF MEASUREMENT, 0.00051[.000020] MIN AT THE END OF AREA G, (LOCALIZED GOLD PLATE AREA), 0.0038[.000150] TIN-LEAD ON LOCALIZED TIN PLATED AREA, ALL OVER 0.0013[.000050] NICKEL
- 2 USE 1.32±0.002[.052±.001] DRILLED HOLE (#55 DRILL). FINISH TO BE TIN OVER 0.02[.001]MIN COPPER.
- 3 DIMENSION APPLIES AT BASE OF SHROUD.
- 4 THE NOTED DIMENSIONS APPLY AT THE MATING FACE OF THE HOUSING.
- 5 0.0038 [1.000150] TIN LEAD ON HOLD DOWN, ALL OVER 0.0013 [1.000050] NICKEL.
6. PACKAGED IN TUBES
- 7 DIMENSIONS NOTED APPLY FROM THE BASIC DIMENSION LINE (NOT THE CIRCUIT CAVITY CENTER LINE) TO THE SURFACE INDICATED.
8. IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS, PLEASE REFER TO THE SPACING PARAGRAPH IN APPLICATION SPEC, #114-7010
9. PACKAGED IN EIA 481 TAPE AND REEL. SEE TABLE FOR TAPE WIDTHS.
- 10 5.5 [1.216] MIN TARGET AREA FOR VACCUM PICK-UP
- 11 HOUSING: LCP,COLOR: BLACK
POST: PHOSPHOR BRONZE
HOLD DOWN: COPPER ALLOY
VACCUUM COVER: ALUMINIUM
- 12 0.00076[.00003] GOLD AT POINT OF MEASUREMENT, 0.00051[.000020] MIN AT THE END POINTS OF AREA G, (LOCALIZED GOLD PLATE AREA), 0.0038[.000150] TIN ON LOCALIZED TIN PLATED AREA, ALL OVER 0.00127[.000050] NICKEL.
- 13 USE 1.55±.02 [1.0610±.0010] DRILLED HOLE (1.55mm DRILL). WITH 0.02(.001) MIN COPPER.
- 14 0.00381 (.000150) TIN ON HOLDDOWN, ALL OVER 0.00127 (.000050) NICKEL



	88mm	65.33 [2.572]	66.59 [2.622]	64.05 [2.522]	49	100	6-2267258-0		
	88mm	58.98 [2.322]	60.248 [2.372]	57.708 [2.272]	44	90	5-2267258-9		
	72mm	52.63 [2.072]	53.89 [2.122]	51.35 [2.022]	39	80	5-2267258-8		
	72mm	46.28 [1.822]	47.54 [1.872]	45.00 [1.772]	34	70	5-2267258-7		
	56mm	39.93 [1.572]	41.19 [1.622]	38.65 [1.522]	29	60	5-2267258-6		
	56mm	33.58 [1.322]	34.84 [1.372]	32.30 [1.272]	24	50	5-2267258-5		
	44mm	27.23 [1.072]	28.49 [1.122]	25.95 [1.022]	19	40	5-2267258-4		
	32mm	20.88 [.822]	22.14 [.872]	19.60 [.772]	14	30	5-2267258-3		
	24mm	14.53 [.572]	15.79 [.622]	13.25 [.522]	9	20	5-2267258-2		
	24mm	8.18 [0.322]	9.44 [.372]	6.90 [.272]	4	10	5-2267258-1		
	88mm	65.33 [2.572]	66.59 [2.622]	64.05 [2.522]	49	100	1-2267258-0		
	88mm	58.98 [2.322]	60.248 [2.372]	57.708 [2.272]	44	90	2267258-9		
	72mm	52.63 [2.072]	53.89 [2.122]	51.35 [2.022]	39	80	2267258-8		
	72mm	46.28 [1.822]	47.54 [1.872]	45.00 [1.772]	34	70	2267258-7		
	56mm	39.93 [1.572]	41.19 [1.622]	38.65 [1.522]	29	60	2267258-6		
	56mm	33.58 [1.322]	34.84 [1.372]	32.30 [1.272]	24	50	2267258-5		
	44mm	27.23 [.1.072]	28.49 [1.122]	25.95 [1.022]	19	40	2267258-4		
	32mm	20.88 [.822]	22.14 [.872]	19.60 [.772]	14	30	2267258-3		
	24mm	14.53 [.572]	15.79 [.622]	13.25 [.522]	9	20	2267258-2		
	24mm	8.18 [0.322]	9.44 [.372]	6.90 [.272]	4	10	2267258-1		
FINISH	TAPE WIDTH	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN RAVI.S CHK J. OLSON APVD J. OLSON	05APR2019 05APR2019 05APR2019	 TE Connectivity HDR ASSY, THROUGH HOLE AMPMODU 50/50 GRID (6.35 [1.250] MATED HEIGHT)			
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-1332 APPLICATION SPEC 114-7010					
MATERIAL 		FINISH SEE TABLE		WEIGHT -					
				CUSTOMER DRAWING		SIZE A1	CAGE CODE 00779	DRAWING NO C=2267258	RESTRICTED TO -
						SCALE 10:1	SHEET 1	OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2267258-5](#)