







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	04APR2019	RS	JO



- 0.00076[.000030] GOLD IN LOCALIZED PLATE AREA 0.00381[.000150] TIN-LEAD ON SOLDER TAILS ALL OVER 0.00127[.000050] NICKEL
- USE 1.55±0.02[.0610±.0010] DRILLED HOLE (1.55mm DRILL). FINISH TO BE TIN/LEAD OVER 0.02[.001] MIN COPPER.
- PLATING 0.0038 [.000150] TIN-LEAD OVER 0.00127 [.000050] NICKEL HOLDDOWN.
- IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS PLEASE REFER TO PARA. 3.3 IN THR APPLICATION SPEC, #114-7010.
- PACKED IN EIA 481 TAPE AND REEL. SEE TABLE FOR TAPE WIDTHS.
- HOUSING: LCP, COLOR-BLACK, CONTACT: COPPER ALLOY
HOLDDOWN: COPPER ALLOY
VACCU COVER: ALLUMINIUM ALLOY
- 0.00076 [.000030] GOLD IN LOCALIZED PLATE AREA 0.00381 [.000150] TIN ON SOLDER TAILS ALL OVER 0.00127 [.000050] NICKEL.
- PLATING 0.0038 [.000150] TIN OVER 0.00127 [.000050] NICKEL HOLDDOWN.
- USE 1.55±0.02[.0610±.0010] DRILLED HOLE (1.55mm DRILL). FINISH TO BE TIN/LEAD OVER 0.02[.001] MIN COPPER.

	88 mm	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	6-2267261-0
	88 mm	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	5-2267261-9
	72 mm	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	5-2267261-8
	72 mm	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	5-2267261-7
	72 mm	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	5-2267261-6
	56 mm	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	5-2267261-5
	56 mm	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	5-2267261-4
	44 mm	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	5-2267261-3
	32 mm	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	5-2267261-2
	32 mm	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	5-2267261-1
	88 mm	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	1-2267261-0
	88 mm	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	2267261-9
	72 mm	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	2267261-8
	72 mm	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	2267261-7
	72 mm	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	2267261-6
	56 mm	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	2267261-5
	56 mm	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	2267261-4
	44 mm	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	2267261-3
	32 mm	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	2267261-2
	32 mm	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	2267261-1
FINISH	TAPE WIDTH	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S	04APR2019	 TE Connectivity				
DIMENSIONS: mm [INCH]		CHK J.OLSON	04APR2019					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.OLSON	04APR2019	NAME ASSY, RECEPTACLE, VERT. DOUBLE ROW, THROUGH HOLE, AMPMODU 50/50 GRID CONNECTOR				
		PRODUCT SPEC						
		108-1332						
		APPLICATION SPEC						
		114-7010						
MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		SEE TABLE		A1	100779	C=2267261	-	
		CUSTOMER DRAWING		SCALE		10:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2267261-8](#)