





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	28MAR16	D.Z	I.Y
	B	REV PER ECR-19-013955	09SEP19	D.Z	W.W



SCALE 5:1



1 NOSE CONE - NYLON. COLOR: SEE TABLE. 25% GLASS FILLED.
DIELECTRIC - POLYESTER PCT. NATURAL. 30% GLASS FILLED.
PIN CONTACT - BRASS.
OUTER SHELL - ZINC.

2 PIN CONTACT - 0.38 µm MIN GOLD ON INTERFACE END.
2.5 µm MIN TIN ON SOLDER END.
BOTH OVER 1.3 µm MIN NICKEL.
OUTER SHELL - 2.0 µm MIN TIN OVER 1.52 µm MIN NICKEL.
BOTH OVER 2.54 µm MAX COPPER.

3 MASS = 3.94g (REFERENCE)


4 VACUUM PICKUP AREA.

5 MINIMUM RECOMMENDED GROUND PLANE.

6 SIGNAL DIMENSION TRACE RECOMMENDED FOR
OPTIMUM SIGNAL PERFORMANCE.

7 MALE INTERFACE PER ISO-20860-1. ROAD VEHICLES 50 Ohm
RADIO FREQUENCY INTERFACE.

8 PACKAGING: TAPE AND REEL.



PER DETAIL Z	WATER BLUE	MATERIAL BRASS	MATERIAL PCT	MATERIAL ZINC ALLOY	Z	2-2291392-0
PER DETAIL N	PASTEL GREEN				N	1-2291392-3
PER DETAIL M	PASTEL ORANGE				M	1-2291392-2
PER DETAIL L	CARMINE RED				L	1-2291392-1
PER DETAIL K	CURRY				K	1-2291392-0
PER DETAIL I	BEIGE				I	2291392-9
PER DETAIL H	HEATHER VIOLET				H	2291392-8
PER DETAIL G	BLUE GREY				G	2291392-7
PER DETAIL F	NUT BROWN				F	2291392-6
PER DETAIL E	LEAF GREEN				E	2291392-5
PER DETAIL D	CLARET VIOLET				D	2291392-4
PER DETAIL C	SIGNAL BLUE				C	2291392-3
PER DETAIL B	CREAM				B	2291392-2
PER DETAIL A	JET BLACK				A	2291392-1
CODING DETAIL	4 NOSE CONE COLOR	3 CENTER PIN	2 DIELECTRIC	1 DIE CASTING	CODING REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ERIC R LOVE 08MAY2015	TE Connectivity			
DIMENSIONS:		CHK ERIC R LOVE 08MAY2015				
mm		APVD ERIC R LOVE 08MAY2015	PRODUCT SPEC		NAME	
			108-32058		MALE ASSEMBLY, STANDOFF	
			APPLICATION SPEC		1 POSITION, PCB, FAKRA	
MATERIAL			SIZE		CAGE CODE	
			WEIGHT		DRAWING NO	
			CUSTOMER DRAWING		RESTRICTED TO	
			SCALE		SHEET	
			10:1		1 OF 2	
					REV	
					B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2291392-3](#)