









LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		INITIAL RELEASE	09SEP2019	AJ	SH
		B		ADDED NEW DASH NUMBER 1-3/1-4	22OCT2019	AJ	SH




1. MATERIAL:
CAGE MATERIAL : 0.25 THICK STAINLESS STEEL.
SPRING MATERIAL: COPPER ALLOY
CLIP MATERIAL: STAINLESS STEEL
HEAT SINK: ALUMINUM
2. FINISH:
SPRING: NICKEL PLATING
HEAT SINK: NICKEL PLATING/BLACK ANODIZING
3. DIMENSION APPLIES WITH MODULE INSTALLED IN THE CAGE TO TOP OF HEAT SINK.
4. REFERENCE APPLICATION SPEC 114-60025 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
5. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.
6. MINIMUM PC BOARD THICKNESS : SINGLES SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN
7. DATUM **-A-** IS TOP SURFACE OF THE HOST BOARD.
8. DATE CODE (YYWD) MARKED APPROXIMATELY AS SHOWN
9. MATES WITH QSFP DD MSA COMPATIBLE TRANSCEIVER.


NICKEL PLATING	22.4	2	1-2327362-6
NICKEL PLATING	25.7	2	1-2327362-4
BLACK ANODIZING	33.0	2	1-2327362-3
BLACK ANODIZING	15.85	2	1-2327362-2
BLACK ANODIZING	19.85	2	1-2327362-1
BLACK ANODIZING	15.85	0	1-2327362-0
BLACK ANODIZING	16.00	0	2327362-9
BLACK ANODIZING	14.7	0	2327362-8
BLACK ANODIZING	18.45	2	2327362-7
NICKEL PLATING	24.4	2	2327362-6
BLACK ANODIZING	13.7	2	2327362-5
NICKEL PLATING	25.7	2	2327362-4
BLACK ANODIZING	14.7	2	2327362-3
NICKEL PLATING	17.2	2	2327362-2
NICKEL PLATING	16.7	2	2327362-1
HEAT SINK FINISH	DIM A	# REAR PINS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 07NOV2017	 TE Connectivity	
		CHK: SEAN HAN 07NOV2017		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: SEAN HAN 07NOV2017	NAME	
		PRODUCT SPEC	CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES ±°	108-60122	SIZE	
		APPLICATION SPEC	A1	
MATERIAL	FINISH	114-60025	DRAWING NO	
		WEIGHT	C=2327362	
CUSTOMER DRAWING		SCALE 2:1 SHEET 1 OF 8 REV B		


LOC		DIST		REVISONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




2327362-6 AS SHOWN




SCALE 4:1




1-2327362-6 AS SHOWN




SCALE 4:1




2327362-7 AS SHOWN
SCALE 4:1



- Z -



2327362-9 AS SHOWN
SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.25
1 PLC ±0.25
2 PLC ±0.20
3 PLC ±0.10
4 PLC ±
ANGLES ±

MATERIAL

-

DWN: ARTHUR JIN 07NOV2017
CHK: SEAN HAN 07NOV2017
APVD: SEAN HAN 07NOV2017

PRODUCT SPEC
108-60122
APPLICATION SPEC
114-60025

WEIGHT
-

CUSTOMER DRAWING



TE Connectivity

CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER



SIZE: A1
CAGE CODE: -
DRAWING NO: C=2327362
RESTRICTED TO: -

SCALE: 2:1
SHEET: 2 OF 8
REV: B



LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	



1-2327362-0 AS SHOWN
SCALE 4:1



1-2327362-1 AS SHOWN
SCALE 4:1




1-2327362-2 AS SHOWN
SCALE 4:1



1-2327362-2 IS SAME AS 1-2327362-0
EXCEPT WITH 2 REAR PINS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARTHUR JIN 07NOV2017	TE Connectivity	
		CHK SEAN HAN 07NOV2017		
		APVD SEAN HAN 07NOV2017	NAME CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
DIMENSIONS:		PRODUCT SPEC 108-60122	SIZE A1	
mm		APPLICATION SPEC 114-60025	CAGE CODE -	
		WEIGHT -	DRAWING NO C=2327362	
MATERIAL -		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 2:1	SHEET 3 OF 8	
		REV B		


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	-



1-2327362-3 AS SHOWN
SCALE 4:1



1-2327362-4 AS SHOWN
SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

ARTHUR JIN

07NOV2017

CHK

SEAN HAN

07NOV2017

APVD

SEAN HAN

07NOV2017

TE Connectivity

CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER

SIZE

A1

CAGE CODE

-

DRAWING NO

2327362

RESTRICTED TO

-

SCALE

2:1

SHEET

4

OF

8

REV

B

DIMENSIONS:

mm

0 PLC

±0.25

1 PLC

±0.25

2 PLC

±0.20

3 PLC

±0.10

4 PLC

±

ANGLES

±

FINISH

-

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±0.25

1 PLC

±0.25

2 PLC

±0.20

3 PLC

±0.10

4 PLC

±

ANGLES

±

FINISH

-

PRODUCT SPEC

108-60122

APPLICATION SPEC


114-60025

WEIGHT


-

CUSTOMER DRAWING


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-




2327362-1 AS SHOWN
SCALE 2:1




2327362-2 AS SHOWN
SCALE 2:1




2327362-3 AS SHOWN
SCALE 2:1




2327362-4 AS SHOWN
SCALE 2:1




1-2327362-4 AS SHOWN
SCALE 2:1




2327362-5 AS SHOWN
SCALE 2:1




2327362-6 AS SHOWN
SCALE 2:1




2327362-7 AS SHOWN
SCALE 2:1




2327362-8 AS SHOWN
SAME AS -3 EXCEPT W/O REAR PINS
SCALE 2:1




2327362-9 AS SHOWN
SCALE 2:1




1-2327362-0 AS SHOWN
SCALE 2:1




1-2327362-1
SCALE 2:1



1-2327362-2 AS SHOWN
SCALE 2:1






1-2327362-3 AS SHOWN
SCALE 2:1




1-2327362-6
SCALE 2:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 07NOV2017	TE Connectivity	
DIMENSIONS:		CHK: SEAN HAN 07NOV2017		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: SEAN HAN 07NOV2017	NAME: CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
	0 PLC ±0.25	PRODUCT SPEC	SIZE: A1 CAGE CODE: - DRAWING NO: C=2327362 RESTRICTED TO: -	
	1 PLC ±0.25	108-60122		
	2 PLC ±0.20	APPLICATION SPEC	SCALE: 2:1 SHEET 5 OF 8 REV B	
	3 PLC ±0.10	114-60025		
MATERIAL: -	ANGLES: ±°	WEIGHT: -	CUSTOMER DRAWING	
	FINISH: -			

4805 (3/11)



LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	ARTHUR JIN		07NOV2017		 TE Connectivity				
				CHK	SEAN HAN		07NOV2017						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	SEAN HAN		07NOV2017		NAME	CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER			
mm				PRODUCT SPEC		108-60122							
		0 PL/C ±0.25 1 PL/C ±0.25 2 PL/C ±0.20 3 PL/C ±0.10 4 PL/C ±0.10		APPLICATION SPEC		114-60025		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH		WEIGHT		CUSTOMER DRAWING		A1	-	C=2327362	-		
								SCALE	2:1	SHEET	7 of 8	REV	B



LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 07NOV2017	TE Connectivity	
DIMENSIONS:		CHK: SEAN HAN 07NOV2017		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: SEAN HAN 07NOV2017	NAME	
0 PLC ±0.25	1 PLC ±0.25	PRODUCT SPEC	CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
2 PLC ±0.20	3 PLC ±0.20	108-60122	SIZE	
4 PLC ±0.10	ANGLES ±	APPLICATION SPEC	CAGE CODE DRAWING NO	
MATERIAL	FINISH	114-60025	RESTRICTED TO	
		WEIGHT	A1 - C=2327362	
CUSTOMER DRAWING		SCALE 2:1	SHEET 8 OF 8	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2327362-6](#) [2327362-4](#)