

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECO-20-013466	24SEP2020	NN	DZ

D

C

B


A

D

C


B

A



1. ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTICTED SUBSTANCES).
2. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
3. ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, AND SIGNAL INTEGRITY.
4. CABLE BEND RADIUS 5X BUNDLE CABLE OD.
5. SEE SHEETS 2 AND 3 FOR WIRING SCHEMATIC.
6. CONNECTORS ARE GEN-Z COMPATIBLE.

△ LABEL INFORMATION SHOWN BELOW:




8. CABLE CONNECTOR MATES WITH TE SLIVER RECEPTACLE P/N 2331813-X, OR 2331814-X.

500	1000 +10/-0	2361347-2
250	500 +10/-0	2361347-1
"M"	"L"	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS 28AUG2019	TE Connectivity	
DIMENSIONS:		CHK R. HENRY 28AUG2019		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME	SLIVER 2.0 2C 33 AWG LATERAL TO LATERAL
	0 PLC	±	PRODUCT SPEC	-
	1 PLC	±	APPLICATION SPEC	-
	2 PLC	±	SIZE	CAGE CODE DRAWING NO
	3 PLC	±	WEIGHT	-
	4 PLC	±	CUSTOMER DRAWING	SCALE 3:2 SHEET 1 OF 2 REV B1
	ANGLES	±		
MATERIAL	SEE BOM	-		
		-		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B. MATTHEWS
CHK
R. HENRY

28AUG2019
28AUG2019

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL
SEE BOM

CUSTOMER DRAWING

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

NAME
SLIVER 2.0 2C 33 AWG
LATERAL TO LATERAL

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=2361347

RESTRICTED TO

SCALE
1:2

SHEET
2

OF
2

REV
B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2361347-1](#)