





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	06MAY2020	AY	PS




- NOTES:
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 μm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TUBE
 - TOLERANCE NOT CUMULATIVE.



2-2373375-0 AS SHOWN

52.10	51.40	50	5-2373375-0
50.10	49.40	48	4-2373375-8
48.10	47.40	46	4-2373375-6
46.10	45.40	44	4-2373375-4
44.10	43.40	42	4-2373375-2
42.10	41.40	40	4-2373375-0
40.10	39.40	38	3-2373375-8
38.10	37.40	36	3-2373375-6
36.10	35.40	34	3-2373375-4
34.10	33.40	32	3-2373375-2
32.10	31.40	30	3-2373375-0
30.10	29.40	28	2-2373375-8
28.10	27.40	26	2-2373375-6
26.10	25.40	24	2-2373375-4
24.10	23.40	22	2-2373375-2
22.10	21.40	20	2-2373375-0
20.10	19.40	18	1-2373375-8
18.10	17.40	16	1-2373375-6
16.10	15.40	14	1-2373375-4
14.10	13.40	12	1-2373375-2
12.10	11.40	10	1-2373375-0
10.10	9.40	8	2373375-8
8.10	7.40	6	2373375-6
DIM "F"	DIM "E"	POS.	TE PN.



RECOMMENDED PCB PATTERN

CONTACT PIN		2	
HOUSING		1	
DESCRIPTION		ITEM NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11NOV2019 CHK 25NOV2019 APVD 27NOV2019	NAME
DIMENSIONS: mm		ANKIT YADAV KARTHIK JK PRASHANTH S.	AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL SMD, SN, TUBE
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-64040	SIZE
0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2° FINISH		APPLICATION SPEC 114-32259	CAGE CODE
MATERIAL SEE NOTES		WEIGHT -	DRAWING NO
-		CUSTOMER DRAWING	RESTRICTED TO
		SCALE 5:1	SHEET 1 OF 1
		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2373375-6](#)