

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

AJ

DIST

16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z	REVISED PER ECO-10-008433	24APR10	HMR	KW

1

COPPER ALLOY

2

TIN-LEAD PL PER ASTM-B-545
2.54μm [.000100] MIN THK, WITH
SUPPLEMENTAL ANTI-FRETTING LUBRICANT.

3

SILVER PL PER QQ-S-365
5.08μm [.000200] MIN THK

4

TIN PLATE PER ASTM-B-545
2.54
SUPPLEMENTAL ANTI-FRETTING LUBRICANT.
μm [.000100] MIN THK, WITH

B ±0.38 [B ±.015]

ϕ A

12.70 [.500]

6.81 [.268]

4

1

9-221132-9

15.24 [.600]

10.67 [.420]

4

1

9-221132-8

SUPERSEDED BY
9-221132-4

12.70 [.500]

5.84 [.230]

4

1

9-221132-7

12.70 [.500]

4.47 [.176]

4

1

9-221132-6

15.24 [.600]

11.30 [.445]

4

1

9-221132-5

12.70 [.500]

5.84 [.230]

4

1

9-221132-4

12.70 [.500]

6.63 [.261]

4

1

9-221132-3

12.70 [.500]

8.46 [.333]

4

1

9-221132-2

12.70 [.500]

6.55 [.258]

4

1

9-221132-1

12.70 [.500]

5.36 [.211]

4

1

9-221132-0

12.70 [.500]

5.61 [.221]

4

1

8-221132-9

OBSOLETE

15.24 [.600]

10.67 [.420]

3

1

3-221132-7

12.70 [.500]

6.81 [.268]

2

1

3-221132-6

12.70 [.500]

4.47 [.176]

2

1

3-221132-3

12.70 [.500]

5.61 [.221]

2

1

3-221132-0

15.24 [.600]

11.30 [.445]

2

1

2-221132-9

12.70 [.500]

5.84 [.230]

2

1

2-221132-6

15.24 [.600]

10.67 [.420]

2

1

2-221132-3

12.70 [.500]

6.63 [.261]

2

1

2-221132-0

OBSOLETE

12.70 [.500]

3.43 [.135]

3

1

1-221132-7

OBSOLETE

12.70 [.500]

6.55 [.258]

3

1

1-221132-4

OBSOLETE

12.70 [.500]

5.61 [.221]

3

1

1-221132-3

OBSOLETE

12.70 [.500]

5.36 [.211]

3

1

1-221132-0

12.70 [.500]

8.46 [.333]

2

1

221132-9

12.70 [.500]

6.55 [.258]

2

1

221132-6

12.70 [.500]

5.36 [.211]

2

1

221132-3

B

A

FINISH

MATERIAL

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

DWN
J.L.GROFT
1-5-90

CHK
R.E.RUTH
1/12/90

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

TYCO
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
-

FERRULE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-221132

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
10:1

SHEET
1

OF
1

REV
Z

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± -
± -
± 0.13 [.005]
± -
± -
± -

± -

FINISH

SEE NOTES

AMP 1470-19 REV 31MAR2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-221132-1](#)