

LOC	DIST	REVISIONS					
AG	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-14-018497	17DEC2014	AP	DG
			B	REVISED PER ECO-15-013876	16MAY2016	JY	SH



1. MATERIALS
- RECEPTACLE HOUSING, LCP, BLACK, UL94V-0 RATED
- SHIELD ASSY: NICKEL SILVER COPPER ALLOY
- CONTACTS: COPPER ALLOY
- EMI SPRING: COPPER ALLOY
- THREADED NUT: BRASS
- CHICKLETS: LCP, BLACK, UL 94V-0 RATED

2. FINISH
- EMI SPRING: TIN PLATE OVER NICKEL PLATE
- NON-PLATED EDGES PERMISSABLE
- THREADED NUT: NICKEL PLATE

3. CONTACT FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION, 108-2462. BASED ON EIA/ECA-364-1000.01A. (CONTROLLED ENVIRONMENT APPLICATIONS) ON MATING END. TIN PLATED ON PCB TAIL


4. THREAD LENGTH OF FASTENER = PCB THICKNESS + 1.45 MAX

5. RECOMMENDED TRACE KEEP OUT ZONE



2214869-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SECHRIST 26MAR2012	NAME RECEPTACLE ASSEMBLY, MINI-SAS HD, 2X	
DIMENSIONS: mm		CHK J. SECHRIST 26MAR2012		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	PRODUCT SPEC 108-2462	
MATERIAL -		FINISH -	APPLICATION SPEC 114-13316	
		WEIGHT -	SIZE A1	
		Customer Drawing	CAGE CODE 00779	
			DRAWING NO 2214869	
			RESTRICTED TO -	
			SCALE 8:1	
			SHEET 1	
			OF 2	
			REV B	



LOC		DIST		REVISIONS			
AG	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	J. SECHRIST	26MAR2012	 TE Connectivity			
				CHK	J. SECHRIST	26MAR2012				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	NAME	RECEPTACLE ASSEMBLY, MINI-SAS HD, 2X			
mm		0 PLC ±" 1 PLC ±" 2 PLC ±" 3 PLC ±" 4 PLC ±"		PRODUCT SPEC	108-2462					
		ANGLES ±"		APPLICATION SPEC	114-13316	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH		WEIGHT	-	A100779	©=2214869	-	-	
				Customer Drawing		SCALE	8:1	SHEET	2 OF 2	
								REV	B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2214869-1](#)