




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-17-016657	14NOV2017	RS	MD
	A1	REVISED PER ECR-18-002379	27FEB2018	BW	MD
	A2	REVISED PER ECO-18-009651	19JUN2018	BKW	MD
	A3	REVISED PER ECR-20-100299	10AUG2020	BDA	WW

- NOTES:
- CONTINUOUS STRIP ON REELS
 - REFERENCE CRIMP INFORMATION:
WIRE RANGE - 22 TO 18AWG
INSULATION RANGE - 1.5 TO 2.8MM,
WIRE BARREL- .080 INCH CRIMP WIDTH, F TYPE
INSULATION BARREL - .130 INCH CRIMP WIDTH, F TYPE
 - RECOMMENDED MATING TAB:
TAB WIDTH 6.3±0.1MM, THICKNESS 0.8±0.03MM
HOLE DIAMETER 1.7MM, CENTER LOCATED 2.5MM FROM TIP

TIN	BRASS	2238136-2
PLAIN BRASS	BRASS	2238136-1
FINISH	MATERIAL	PART NO

TE Connectivity			
NAME RECEPTACLE, POSITIVE-LOCK, RAST 6.35 SERIES			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-2238136	-
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
		REV A3	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±1.00 1 PLC ±0.50 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL BRASS	FINISH SEE TABLE

DWN J. POTERJOY	06DEC2016
CHK F. LUPO	06DEC2016
APVD R. ROBONE	06DEC2016
PRODUCT SPEC	108-143029
APPLICATION SPEC	114-2074
WEIGHT	-
CUSTOMER DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2238136-2](#)