









RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE



2-2842269-0 AS SHOWN

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	06DEC2019	AY	PS
	A1	REMOVE POSITION 4	04JUN2020	AY	PS

- NOTES:
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 µm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TAPE AND REEL.
 - TOLERANCE NOT CUMULATIVE.

52.10	51.40	50	5-2842269-0
50.10	49.40	48	4-2842269-8
48.10	47.40	46	4-2842269-6
46.10	45.40	44	4-2842269-4
44.10	43.40	42	4-2842269-2
42.10	41.40	40	4-2842269-0
40.10	39.40	38	3-2842269-8
38.10	37.40	36	3-2842269-6
36.10	35.40	34	3-2842269-4
34.10	33.40	32	3-2842269-2
32.10	31.40	30	3-2842269-0
30.10	29.40	28	2-2842269-8
28.10	27.40	26	2-2842269-6
26.10	25.40	24	2-2842269-4
24.10	23.40	22	2-2842269-2
22.10	21.40	20	2-2842269-0
20.10	19.40	18	1-2842269-8
18.10	17.40	16	1-2842269-6
16.10	15.40	14	1-2842269-4
14.10	13.40	12	1-2842269-2
12.10	11.40	10	1-2842269-0
10.10	9.40	8	2842269-8
8.10	7.40	6	2842269-6
DIM "F"	DIM "E"	POS.	TE PN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± -
	1 PLC ± -
	2 PLC ± 0.25
	3 PLC ± -
	4 PLC ± -
	ANGLES ± 2°
MATERIAL	FINISH
SEE NOTES	SEE NOTES
-	-
DWN	29NOV2019
CHK	ANKIT YADAV
APVD	04DEC2019
PRASHANTH S.	KARTHIK JK
PRODUCT SPEC	108-64040
APPLICATION SPEC	114-32259
WEIGHT	-
CUSTOMER DRAWING	SCALE 7:1
SHEET 1 OF 1	REV A1
TE Connectivity	
AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE, Sn, TR	
SIZE	CAGE CODE
A2	00779
DRAWING NO	2842269
RESTRICTED TO	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2842269-8](#)