




4		3		2		1																																																					
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS																																																			
© COPYRIGHT – By –		ALL RIGHTS RESERVED.		H		—		P		LTR		DESCRIPTION		DATE		DWN		APVD																																									
NOTES: Tolerances cable lengths: 0m to 0.5m +30mm 0.5m to 1.0m +50mm 1.0m to 3.0m +100mm < 3.0m +1.5%										A		INITIAL RELEASE		12NOV2013		GSK		BvH																																									
										A1		ECR–14–011671		14AUG2014		GSK		BvH																																									
TECHNICAL DATA																																																											
Operating voltage										max. 60 V AC/DC																																																	
Operating current per contact										max. 4 A																																																	
Locking of ports										Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self–securing																																																	
Protection										IP65 and IP67 when plugged and screwed down (EN 60529)																																																	
PUR CABLE																																																											
No./diameter of wires										3 x 0.34 mm²																																																	
Wire isolation										PP (br, bl, bk)																																																	
C–track properties										5 million																																																	
Jacket										PUR (UL/CSA)																																																	
Outer diameter										approx. 5.0 mm																																																	
Bend radius (moving)										10 x outer diameter																																																	
Temperature range (fixed)										–40...+80 °C																																																	
Temperature range (mobile)										–25...+80 °C																																																	
PVC CABLE																																																											
No./diameter of wires										3 X 0.34 mm²																																																	
Wire isolation										PVC (br, bl, bk)																																																	
C–track properties																																																											
Jacket										PVC (UL/CSA)																																																	
Outer diameter										approx. 5.0 mm																																																	
Bend radius (moving)										10 x outer diameter																																																	
Temperature range (fixed)										–30...+80 °C																																																	
Temperature range (mobile)										–5...+80 °C																																																	
										Schematic diagram																																																	
3 pos										10mtr										PVC		Black		1–2273005–4		3x22AWG PVC 10.0m		8																															
3 pos										5mtr										PVC		Black		1–2273005–3		3x22AWG PVC 5.0m		7																															
3 pos										3mtr										PVC		Black		1–2273005–2		3x22AWG PVC 3.0m		6																															
3 pos										1.5mtr										PVC		Black		1–2273005–1		3x22AWG PVC 1.5m		5																															
3 pos										10mtr										PUR		Black		2273005–4		3x22AWG PUR 10.0m		4																															
3 pos										5mtr										PUR		Black		2273005–3		3x22AWG PUR 5.0m		3																															
3 pos										3mtr										PUR		Black		2273005–2		3x22AWG PUR 3.0m		2																															
3 pos										1.5mtr										PUR		Black		2273005–1		3x22AWG PUR 1.5m		1																															
LENGTH”L”										MATERIAL										JACKET COLOR										TE PN										DESCRIPTION										ITEM									
THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN 12NOV2013 SATHISH KUMAR .G										 TE Connectivity																																							
CHK 12NOV2013 B.VELDHOVEN										APVD 12NOV2013 A.VAN ZANDVOORT																																																	
DIMENSIONS: mm										TOLERANCES UNLESS OTHERWISE SPECIFIED:										NAME																																							
										0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –										PRODUCT SPEC 108–19483																																							
MATERIAL –										FINISH –										APPLICATION SPEC 114–32127																																							
																				WEIGHT –																																							
CUSTOMER DRAWING										SCALE NTS										SHEET 1 OF 1										REV A1																													

1470–19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2273005-4](#)