




NOTES:


1. MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.38 μ m GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 μ m TIN OVER NICKEL UNDER PLATING.

2. PACKAGING: TAPE AND REEL

3. TOLERANCE NOT CUMULATIVE.



52.10	51.40	50	5-2842271-0
50.10	49.40	48	4-2842271-8
48.10	47.40	46	4-2842271-6
46.10	45.40	44	4-2842271-4
44.10	43.40	42	4-2842271-2
42.10	41.40	40	4-2842271-0
40.10	39.40	38	3-2842271-8
38.10	37.40	36	3-2842271-6
36.10	35.40	34	3-2842271-4
34.10	33.40	32	3-2842271-2
32.10	31.40	30	3-2842271-0
30.10	29.40	28	2-2842271-8
28.10	27.40	26	2-2842271-6
26.10	25.40	24	2-2842271-4
24.10	23.40	22	2-2842271-2
22.10	21.40	20	2-2842271-0
20.10	19.40	18	1-2842271-8
18.10	17.40	16	1-2842271-6
16.10	15.40	14	1-2842271-4
14.10	13.40	12	1-2842271-2
12.10	11.40	10	1-2842271-0
10.10	9.40	8	2842271-8
8.10	7.40	6	2842271-6
DIM "F"	DIM "E"	POS.	TE PN.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02DEC2019 ANKIT YADAV CHK 04DEC2019 KARTHIK JK APVD 05DEC2019 PRASHANTH S.		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 2°		NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE, 0.38 Au, TR	
		PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259		SIZE A2	
MATERIAL SEE NOTES -		FINISH SEE NOTES -		CAGE CODE 00779	
		WEIGHT -		DRAWING NO 2842271	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 7:1	
				SHEET 1 of 1	
				REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2842271-8](#)