




[illegible]

1. MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.38 μ m GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 μ m TIN OVER NICKEL UNDER PLATING.

3

TOLERANCE NOT CUMULATIVE.



Technical drawing of a 2x8 grid of holes. The drawing includes the following dimensions and callouts:

- Overall width: 2.00
- Overall height: 2.00
- Top hole diameter: $\varnothing 0.80 \pm 0.05$ TYP
- Bottom hole diameter: $\varnothing 0.1$ (with a note: (FINISHED HOLE))
- Minimum hole diameter: $\varnothing 1.20$ MIN TYP

RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV	12NOV2019
DIMENSIONS:		CHK KARTHIK J	25NOV2019
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S.	27NOV2019
mm	0 PLC ±0 1 PLC ±0.1 2 PLC ±0.25 3 PLC ±0.5 4 PLC ±1 ANGLES ±2°	PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259	
MATERIAL	FINISH	WEIGHT	
SEE NOTES	-	-	
-	-	CUSTOMER DRAWING	

		TE Connectivity	
NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, VERTICAL TH, 0.38 Au, TUBE, WITH PICK AND PLACE CAP			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	Ⓒ=2842303	-
		SCALE 5:1	SHEET 1 OF 1
		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2842303-6](#)