

4

3

2

1

THIS DRAWING IS UNPUBLISHED DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION

© COPYRIGHT- TE CONNECTIVITY

ALL RIGHTS RESERVED

REVISIONS

REV	DESCRIPTION /MODIFICATIONS	DATE	DWN	APVD
1	NEW DRAWING	06APR2020		GS

**Thin-wall, flexible and flame-retarded heat-shrinkable tubing**

**Installation**

Minimum shrink temperature 95°C [203°F]  
Minimum full recovery temperature 121°C [250°F]

**Operating Temperature Range**

-55°C to 135°C  
[-67°F to 275°F]

**Application**

Designed to provide superior mechanical (abrasion, cut-through, and strain relief), thermal, and fluid-resistance performance in demanding environments. Widely used to provide insulation strain relief of wire terminations and connections. Used for jacketing wire bundles and light duty harnesses where superior abrasion resistance is a plus, Also used to identify and color code electrical connectors and wire bundles.

Size	Inside Diameter		Recovered Wall Thickness** After Heating
	Minimum Expanded as Supplied	Maximum Recovered After Heating	
3/64	1.2 [0.046]	0.6 [0.023]	0.40 ± 0.08 [0.016 ± 0.003]
1/16	1.6 [0.063]	0.8 [0.031]	0.43 ± 0.08 [0.017 ± 0.003]
3/32	2.4 [0.093]	1.2 [0.046]	0.51 ± 0.08 [0.020 ± 0.003]
1/8	3.2 [0.125]	1.6 [0.062]	0.51 ± 0.08 [0.020 ± 0.003]
3/16	4.8 [0.187]	2.4 [0.093]	0.51 ± 0.08 [0.020 ± 0.003]
1/4	6.4 [0.250]	3.2 [0.125]	0.64 ± 0.08 [0.025 ± 0.003]
3/8	9.5 [0.375]	4.8 [0.187]	0.64 ± 0.08 [0.025 ± 0.003]
1/2	12.7 [0.500]	6.4 [0.250]	0.64 ± 0.08 [0.025 ± 0.003]
3/4	19.1 [0.750]	9.5 [0.375]	0.76 ± 0.08 [0.030 ± 0.003]
1	25.4 [1.000]	12.7 [0.500]	0.89 ± 0.12 [0.035 ± 0.005]
1 1/4	31.8 [1.250]	15.9 [0.625]	1.02 ± 0.15 [0.040 ± 0.006]
1 1/2	38.1 [1.500]	19.1 [0.750]	1.02 ± 0.15 [0.040 ± 0.006]
2	50.8 [2.000]	25.4 [1.000]	1.14 ± 0.16 [0.045 ± 0.007]
3	76.2 [3.000]	38.1 [1.500]	1.27 ± 0.20 [0.050 ± 0.008]
4	101.6 [4.000]	50.8 [2.000]	1.40 ± 0.23 [0.055 ± 0.009]
5	127.0 [5.000]	63.5 [2.500]	1.52 ± 0.23 [0.060 ± 0.009]

COLOR	Standard	Black (-0, BK), white (-9, WH), red (-2, RD), blue (-6, BU), yellow (-4, YO), green (-5, GN), clear (-X, CL)
	Nonstandard	Brown (-1, BN), Orange (-3, OR), Violet (-7, VT), Gray (-8, GY)
Size selection	Always order the largest size that will shrink snugly over the component to be covered, Special order sizes are available upon request	
Standard packaging	On spools or 1.2 meter [4 foot] lengths.	
Ordering description***	Specify product name, size and color (for example, RNF-100 1/4-0 [Europe] or RNF-100 1/4-BK [Americas])	

\*\*\*Europe only. For supply to MIL, DefStan and BS add -MS, -DS or -BS to ordering description

Features	
Shrink Ratio	3:1
Temperature range	-40°C to +135°C
Flammability (IEC 60684-2 method A)	Self-extinguishing 60 sec. max.
Color	Black
Delivery Form	on spools, uncoated

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWM			
DIMENSIONS: mm		CHK GREG S			
		APVD GREG S		NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RNF 100	
MATERIAL		FINISH		PRODUCT SPEC	-
-		-		APPLICATION SPEC	-
-		-		SIZE FORMAT	A3
-		-		CAGE CODE	-
-		-		DRAWING NO	EPD-202-32012-01
-		-		RESTRICTED TO	-
CUSTOMER DRAWING				SCALE	NTS
				SHEET	1 OF 2
				REV	1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EE1123-000](#)