


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
6		REVISED PER ECR-21-001415	03FEB2021	S.S	N.S

- NOTES:
1. MATERIAL:
- 1.1 HOUSING: HIGH TEMPERATURE THERMO PLASTIC,UL94V-0,COLOR:BLACK.
- 1.2 CONTACT: COPPER ALLOY.
- 1.3 SOLDER PEG AND LATCH:STAINLESS STEEL.
2. FINISH:
- SOLDER PEG: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- CONTACT SOLDER AREA: GOLD FLASH ON SOLDERTAIL.
- 2.1 CONTACT AREA: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.2 CONTACT AREA: 5u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.3 CONTACT AREA: 10u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.4 CONTACT AREA: 15u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.5 CONTACT AREA: 30u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
3. COPLANARITY: 0.10 MAX. (BEFORE SOLDERRING)



MATING/UNMATING VIEW  
SCALE 2:1

MATING: ① INSERTING(25°) → ② ROTATING → ③ FIXED  
UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

PACKAGE TYPE 2	BLACK	1.2V	GF	260	2309413-6
PACKAGE TYPE 1	BLACK	1.2V	30u"	260	2309413-5
PACKAGE TYPE 1	BLACK	1.2V	15u"	260	2309413-4
PACKAGE TYPE 1	BLACK	1.2V	10u"	260	2309413-3
PACKAGE TYPE 1	BLACK	1.2V	5u"	260	2309413-2
PACKAGE TYPE 1	BLACK	1.2V	GF	260	2309413-1
PACKING TYPE	HOUSING COLOR	POWER SUPPLY	FINISH	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± 0.25  
2 PLC ± 0.15  
3 PLC ± 0.10  
4 PLC ± 0  
ANGLES ± -  
FINISH

DWN DAVID ZHAO 09SEP2016  
CHK RICHARD MA 09SEP2016  
APVD SIMON LI 09SEP2016  
PRODUCT SPEC 108-115122  
APPLICATION SPEC -  
WEIGHT -  
CUSTOMER DRAWING

TE Connectivity





DDR4 SODIMM SOCKET  
0.5mm PITCH 260POS  
9.2mm HEIGHT STANDARD TYPE

SIZE A2  
CAGE CODE 00779  
DRAWING NO C-2309413  
RESTRICTED TO


SECTION:A-A  
SCALE 2:1

1471-9 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




RECOMMEND PCB LAYOUT  
THE TOLERANCE UNLESS SPECIFIED IS ±0.05MM








DETAIL:D  
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
DIMENSIONS: mm		CHK RICHARD MA 09SEP2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SIMON LI 09SEP2016			
MATERIAL		PRODUCT SPEC			
APPLICATION SPEC		NAME	DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 9.2mm HEIGHT STANDARD TYPE		
WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING		A2	00779	C=2309413	
SCALE 1:1		SHEET 2 OF 5		REV 6	


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



PULL OUT DIRECTION 




250	2	500	2309413-5
250	2	500	2309413-4
250	2	500	2309413-3
250	2	500	2309413-2
250	2	500	2309413-1
PCS/ REEL	REEL/ CARTON	PCS/ CARTON	PART NUMBER






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	 TE Connectivity	
		CHK RICHARD MA 09SEP2016		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED.	APVD SIMON LI 09SEP2016	NAME	
mm	0 PLC ± 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 9.2mm HEIGHT STANDARD TYPE	
MATERIAL	FINISH	APPLICATION SPEC	SIZE	RESTRICTED TO
		WEIGHT	A2	
CUSTOMER DRAWING			CAGE CODE	DRAWING NO
			00779	C=2309413
			SCALE	SHEET
			—	3 of 5
			REV	6

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE TYPE 2



PULL OUT DIRECTION



250	2	500	2309413-6
PCS/REEL	REEL/CARTON	PCS/CARTON	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID_ZHAO 09SEP2016	TE Connectivity	
		CHK RICHARD_MA 09SEP2016		
DIMENSIONS: mm		APVD SIMON_LI 09SEP2016	NAME	
		PRODUCT SPEC	DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 9.2mm HEIGHT STANDARD TYPE	
		APPLICATION SPEC		
MATERIAL		WEIGHT	SIZE A2	RESTRICTED TO
			CAGE CODE 00779	
			DRAWING NO C=2309413	
		CUSTOMER DRAWING	SCALE	SHEET 4 of 5
			REV 6	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2309413-4](#)