



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AB5	REVISED PER ECO-13-005565	02APR13	KH	JO



 ROHS 2002/95/EC COMPLIANT

RECOMMENDED PC BOARD HOLE PATTERN
PC BOARD THICKNESS 1.57[.062]



- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED 0.76 μ m[.000030] GOLD IN CONTACT AREA, 3.81–7.62 μ m[.000150–.000300] BRIGHT TIN–LEAD ON LEADS, ALL OVER 1.27 μ m[.000050] MINIMUM NICKEL
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO CONTACT LOCATIONS
- 4 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN,EITHER SIDE.
- 5 TOLERANCE IS NON–CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.
- 7 POINT–OF–MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT–OF–CONTACT DIMENSION.
- 9 TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- 10 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 11 CONTACT:DUPLEX PLATED 0.76 MICROMETERS(.000030) MIN GOLD IN CONTACT AREA,3.81–7.62 MICROMETERS(.000150–.000300) MATTE TIN ON LEADS, ALL OVER 1.27 MICROMETERS (.000050) MINIMUM NICKEL.



SUPERSEDED BY 8-534267-4	2	96.52[3.800]	99.06[3.900]	78	4-534267-0
	2	91.44[3.600]	93.98[3.700]	74	3-534267-9
	2	88.90[3.500]	91.44[3.600]	72	3-534267-8
	2	86.36[3.400]	88.90[3.500]	70	3-534267-7
	2	83.82[3.300]	86.36[3.400]	68	3-534267-6
	2	81.28[3.200]	83.82[3.300]	66	3-534267-5
	2	78.74[3.100]	81.28[3.200]	64	3-534267-4
	2	76.20[3.000]	78.74[3.100]	62	3-534267-3
	2	71.12[2.800]	73.66[2.900]	58	3-534267-2
	2	68.58[2.700]	71.12[2.800]	56	3-534267-1
	2	66.04[2.600]	68.58[2.700]	54	3-534267-0
	2	63.50[2.500]	66.04[2.600]	52	2-534267-9
	2	55.88[2.200]	58.42[2.300]	46	2-534267-8
	2	53.34[2.100]	55.88[2.200]	44	2-534267-7
	2	50.80[2.000]	53.34[2.100]	42	2-534267-6
	2	45.72[1.800]	48.26[1.900]	38	2-534267-5
	2	40.64[1.600]	43.18[1.700]	34	2-534267-4
	2	38.10[1.500]	40.64[1.600]	32	2-534267-3
	2	33.02[1.300]	35.56[1.400]	28	2-534267-2
	10	2	25.40[1.000]	27.94[1.100]	22
2		12.70[.500]	15.24[.600]	12	2-534267-0
2		17.78[.700]	20.32[.800]	16	1-534267-9
2		60.96[2.400]	63.50[2.500]	50	1-534267-8
2		2.54[.100]	5.08[.200]	4	1-534267-7
2		93.98[3.700]	96.52[3.800]	76	1-534267-6
2		43.18[1.700]	45.72[1.800]	36	1-534267-5
2		5.08[.200]	7.62[.300]	6	1-534267-4
2			2.54[.100]	2	1-534267-3
2		35.56[1.400]	38.10[1.500]	30	1-534267-2
10	2	58.42[2.300]	60.96[2.400]	48	1-534267-1
	2	20.32[.800]	22.86[.900]	18	1-534267-0
	2	27.94[1.100]	30.48[1.200]	24	534267-9
	2	73.66[2.900]	76.20[3.000]	60	534267-8
	2	48.26[1.900]	50.80[2.000]	40	534267-7
	2	30.48[1.200]	33.02[1.300]	26	534267-6
	2	7.62[.300]	10.16[.400]	8	534267-5
	2	99.06[3.900]	101.60[4.000]	80	534267-4
	2	10.16[.400]	12.70[.500]	10	534267-3
	2	22.86[.900]	25.40[1.000]	20	534267-2
10	2	15.24[.600]	17.78[.700]	14	534267-1
	FINISH	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002		 TE Connectivity	
		CHK J.OLSON 06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD J.OLSON 06NOV02			
		PRODUCT SPEC 108-25022			
		APPLICATION SPEC 114-25018			
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		SIZE A2		CAGE CODE 00779	
MATERIAL		FINISH		DRAWING NO G-534267	
		 		RESTRICTED TO -	
		WEIGHT -		SCALE 4:1	
CUSTOMER DRAWING				SHEET 1 of 2	
				REV AB5	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

		$\triangle_{11}$	96.52[3.800]	99.06[3.900]	78	$\triangle_{12}$	9-534267-0
		$\triangle_{11}$	91.44[3.600]	93.98[3.700]	74	$\triangle_{12}$	8-534267-9
		$\triangle_{11}$	88.90[3.500]	91.44[3.600]	72	$\triangle_{12}$	8-534267-8
		$\triangle_{11}$	86.36[3.400]	88.90[3.500]	70	$\triangle_{12}$	8-534267-7
		$\triangle_{11}$	83.82[3.300]	86.36[3.400]	68	$\triangle_{12}$	8-534267-6
		$\triangle_{11}$	81.28[3.200]	83.82[3.300]	66	$\triangle_{12}$	8-534267-5
		$\triangle_{11}$	78.74[3.100]	81.28[3.200]	64	$\triangle_{12}$	8-534267-4
		$\triangle_{11}$	76.20[3.000]	78.74[3.100]	62	$\triangle_{12}$	8-534267-3
		$\triangle_{11}$	71.12[2.800]	73.66[2.900]	58	$\triangle_{12}$	8-534267-2
		$\triangle_{11}$	68.58[2.700]	71.12[2.800]	56	$\triangle_{12}$	8-534267-1
		$\triangle_{11}$	66.04[2.600]	68.58[2.700]	54	$\triangle_{12}$	8-534267-0
		$\triangle_{11}$	63.50[2.500]	66.04[2.600]	52	$\triangle_{12}$	7-534267-9
		$\triangle_{11}$	55.88[2.200]	58.42[2.300]	46	$\triangle_{12}$	7-534267-8
		$\triangle_{11}$	53.34[2.100]	55.88[2.200]	44	$\triangle_{12}$	7-534267-7
		$\triangle_{11}$	50.80[2.000]	53.34[2.100]	42	$\triangle_{12}$	7-534267-6
		$\triangle_{11}$	45.72[1.800]	48.26[1.900]	38	$\triangle_{12}$	7-534267-5
		$\triangle_{11}$	40.64[1.600]	43.18[1.700]	34	$\triangle_{12}$	7-534267-4
		$\triangle_{11}$	38.10[1.500]	40.64[1.600]	32	$\triangle_{12}$	7-534267-3
		$\triangle_{11}$	33.02[1.300]	35.56[1.400]	28	$\triangle_{12}$	7-534267-2
		$\triangle_{11}$	25.40[1.000]	27.94[1.100]	22	$\triangle_{12}$	7-534267-1
		$\triangle_{11}$	12.70[.500]	15.24[.600]	12	$\triangle_{12}$	7-534267-0
		$\triangle_{11}$	17.78[.700]	20.32[.800]	16	$\triangle_{12}$	6-534267-9
		$\triangle_{11}$	60.96[2.400]	63.50[2.500]	50	$\triangle_{12}$	6-534267-8
$\triangle_{10}$		$\triangle_{11}$	2.54[.100]	5.08[.200]	4	$\triangle_{12}$	6-534267-7
		$\triangle_{11}$	93.98[3.700]	96.52[3.800]	76	$\triangle_{12}$	6-534267-6
		$\triangle_{11}$	43.18[1.700]	45.72[1.800]	36	$\triangle_{12}$	6-534267-5
$\triangle_{10}$	$\triangle_{10}$	$\triangle_{11}$	5.08[.200]	7.62[.300]	6	$\triangle_{12}$	6-534267-4
$\triangle_{10}$	OBSOLETE	$\triangle_{11}$	-	2.54[.100]	2	$\triangle_{12}$ $\triangle_6$	6-534267-3
		$\triangle_{11}$	35.56[1.400]	38.10[1.500]	30	$\triangle_{12}$	6-534267-2
		$\triangle_{11}$	58.42[2.300]	60.96[2.400]	48	$\triangle_{12}$	6-534267-1
		$\triangle_{11}$	20.32[.800]	22.86[.900]	18	$\triangle_{12}$	6-534267-0
		$\triangle_{11}$	27.94[1.100]	30.48[1.200]	24	$\triangle_{12}$	5-534267-9
		$\triangle_{11}$	73.66[2.900]	76.20[3.000]	60	$\triangle_{12}$	5-534267-8
		$\triangle_{11}$	48.26[1.900]	50.80[2.000]	40	$\triangle_{12}$	5-534267-7
		$\triangle_{11}$	30.48[1.200]	33.02[1.300]	26	$\triangle_{12}$	5-534267-6
$\triangle_{10}$		$\triangle_{11}$	7.62[.300]	10.16[.400]	8	$\triangle_{12}$	5-534267-5
		$\triangle_{11}$	99.06[3.900]	101.60[4.000]	80	$\triangle_{12}$	5-534267-4
$\triangle_{10}$		$\triangle_{11}$	10.16[.400]	12.70[.500]	10	$\triangle_{12}$	5-534267-3
		$\triangle_{11}$	22.86[.900]	25.40[1.000]	20	$\triangle_{12}$	5-534267-2
		$\triangle_{11}$	15.24[.600]	17.78[.700]	14	$\triangle_{12}$	5-534267-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>M.BINNER</u> 06NOV2002 CHK <u>J.OLSON</u> 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD <u>J.OLSON</u> 06NOV02 PRODUCT SPEC <u>108-25022</u> APPLICATION SPEC <u>114-25018</u>		SIZE A2	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C=534267	
CUSTOMER DRAWING				RESTRICTED TO -	
				SCALE 1:1	
				SHEET 2 of 2	
				REV AB5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-534267-9](#)