

# SPECIFICATION CONTROL DRAWING

SCD

**55LF0122**


Title TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, ULTRA LOW FLUORIDE, GENERAL PURPOSE, 600 VOLT

Date 10-17-18

Revision C

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55LF0112



CABLE CONSTRUCTION DETAILS				
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
		NOMINAL	MAXIMUM	
55LF0122-30-*	30	.048	.052	1.4
55LF0122-28-*	28	.054	.058	1.9
55LF0122-26-*	26	.064	.068	2.9
55LF0122-24-*	24	.074	.078	4.1
55LF0122-22-*	22	.086	.090	5.7
55LF0122-20-*	20	.100	.104	8.8
55LF0122-18-*	18	.120	.124	13.3
55LF0122-16-*	16	.136	.140	16.9
55LF0122-14-*	14	.170	.176	26.5
55LF0122-12-*	12	.206	.212	40.2

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

COMPONENT WIRE COLOR: Per MIL-STD-681,

except light colors (xL) shall meet Munsell color limits for UV laser markable wire in SAE AS22759.

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

INSULATION FLAWS:

Spark Test, 5.7 kV (rms) at 3 kHz

Impulse Dielectric Test, 8.0 kV (peak)

1/ PART NUMBER:

The "\*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors.

Example: AWG 22, light blue and white component wires: 55LF0122-22-6L/9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681, EXCEPT LIGHT COLORS SHALL BE DESIGNATED WITH AN "L" AFTER THE COLOR CODE (0L, 1L, 2L, etc.). HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Raychem, TE Connectivity, and TE connectivity (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



**Raychem Wire & Cable**  
501 Oakside Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-522-6752  
Fax: 1-650-361-6297

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55LF0122-20-9/96CS3293](#) [55LF0122-22-9/96CS3293](#)