

2018

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.


BY Tyco Electronics AMP GmbH
© COPYRIGHT 2018

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11JUL2018	GK	ES

NOTES:

- 1 COPPER ALLOY.
- 2 GOLD PLATED OVER NICKEL
3. DURABILITY: 250 MATING CYCLES
4. MAX CURRENT 7A
MAX CONTACT RESISTANCE 10MΩ



	0.18	0.64	24-28	2334110-4
NOT IN PRODUCTION	0.17	0.90	22-24	2334110-3
	0.16	1.12	20-24	2334110-2
NOT IN PRODUCTION	0.18	1.36	18	2334110-1
WEIGHT (g)	D	AWG	PART NO	

DIMENSIONS: mm		DWN GOPALAKRISHNA HV 18APR2018		MATERIAL		FINISH	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK E STELLINGA 18APR2018		 TE Connectivity			
		APVD E STELLINGA 18APR2018					
		PRODUCT SPEC		NAME PIN CRIMP CONTACT AWG 18-28			
		APPLICATION SPEC		SIZE A 4			
WEIGHT SEE TABLE		CAGE CODE 00779		DRAWING NO C-2334110		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2334110-2](#)