




- 1.27 μm [.000050] MIN BRIGHT TIN OVER 1.27 μm [.000050] MIN NICKEL.
2.54 μm [.000100] MIN NICKEL OVER 5.08 μm [.000200] MIN COPPER.
3 PARTS INDIVIDUALLY BULK PACKAGED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-16-005483	13APR2016	AP	DG

FEMALE	8.89 [.350]	5787543-9
FEMALE	10.16 [.400]	5787543-8
FEMALE	11.43 [.450]	5787543-7
MALE	8.89 [.350]	5787543-3
MALE	10.16 [.400]	5787543-2
MALE	11.43 [.450]	5787543-1
JACKSCREW	CABLE MAX DIA.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN: G. PETERS 26AUG05 CHK: S. SHUEY 26AUG05 APVD: M. WALMSLEY 26AUG05		 TE Connectivity									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		BACKSHELL KIT, UNASSEMBLED, 40 POSITION .050 SERIES AMPLIMITE									
mm		0 PLC ± - 1 PLC ± - 2 PLC ± 0.38[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		A1 00779		5787543		SCALE		1:1		SHEET 1 OF 1 REV B	
				0.000000		CUSTOMER DRAWING									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5787543-3](#)