




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		AB1	REVISED PER ECO-11-004820	11MAR11	RK HMR
			AB2	REVISED PER ECR-14-016482	04NOV14	L.P T.D
			AB3	REVISED PER ECR-18-001453	1APR2020	MK EW



- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE — 16 OUNCES MIN INITIALLY.
6 OUNCES MIN AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN.
- 4 .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.

OBSOLETE	NYLON 6/6; WHITE	BRASS — GOLD	3-582118-9
	NYLON 6/6; GRAY	BRASS — GOLD	3-582118-8
	NYLON 6/6; VIOLET	BRASS — GOLD	3-582118-7
	NYLON 6/6; BLUE	BRASS — GOLD	3-582118-6
	NYLON 6/6; GREEN	BRASS — GOLD	3-582118-5
	NYLON 6/6; YELLOW	BRASS — GOLD	3-582118-4
	NYLON 6/6; ORANGE	BRASS — GOLD	3-582118-3
	NYLON 6/6; RED	BRASS — GOLD	3-582118-2
OBSOLETE	NYLON 6/6; BROWN	BRASS — GOLD	3-582118-1
	NYLON 6/6; BLACK	BRASS — GOLD	3-582118-0
	NYLON 6/6; WHITE	BRASS — SILVER	2-582118-9
OBSOLETE	NYLON 6/6; GRAY	BRASS — SILVER	2-582118-8
OBSOLETE	NYLON 6/6; VIOLET	BRASS — SILVER	2-582118-7
OBSOLETE	NYLON 6/6; BLUE	BRASS — SILVER	2-582118-6
OBSOLETE	NYLON 6/6; GREEN	BRASS — SILVER	2-582118-5
OBSOLETE	NYLON 6/6; YELLOW	BRASS — SILVER	2-582118-4
OBSOLETE	NYLON 6/6; ORANGE	BRASS — SILVER	2-582118-3
	NYLON 6/6; RED	BRASS — SILVER	2-582118-2
	NYLON 6/6; BROWN	BRASS — SILVER	2-582118-1
	NYLON 6/6; BLACK	BRASS — SILVER	2-582118-0
	NYLON 6/6; WHITE	BRASS — TIN	1-582118-9
	NYLON 6/6; GRAY	BRASS — TIN	1-582118-8
	NYLON 6/6; VIOLET	BRASS — TIN	1-582118-7
OBSOLETE	NYLON 6/6; BLUE	BRASS — TIN	1-582118-6
	NYLON 6/6; GREEN	BRASS — TIN	1-582118-5
	NYLON 6/6; YELLOW	BRASS — TIN	1-582118-4
OBSOLETE	NYLON 6/6; ORANGE	BRASS — TIN	1-582118-3
OBSOLETE	NYLON 6/6; RED	BRASS — TIN	1-582118-2
OBSOLETE	NYLON 6/6; BROWN	BRASS — TIN	1-582118-1
OBSOLETE	NYLON 6/6; BLACK	BRASS — TIN	1-582118-0

HOUSING — MATERIAL; COLOR		RECEPTACLE — MATERIAL; FINISH		PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 13APR2004	 TE Connectivity			
DIMENSIONS: mm		CHK E. HOWARD 13APR2004				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD 13APR2004	NAME			
		PRODUCT SPEC	ASSEMBLY, TEST PROBE			
		—	—			
		APPLICATION SPEC	—			
		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A2 00779		C=582118	—
SEE TABLE	SEE TABLE	CUSTOMER DRAWING		SCALE	SHEET	REV
				6:1	1 of 1	AB3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-582118-4](#)