


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		AB1	REVISED PER ECO-11-004820	11MAR11	RK HMR
			AB2	REVISED PER ECR-14-016482	04NOV14	L.P T.D
			AB3	REVISED PER ECR-18-001453	1APR2020	MK EW



- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE — 16 OUNCES MIN INITIALLY.
6 OUNCES MIN AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN.
- 4 .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.

OBSOLETE	NYLON 6/6; WHITE	BRASS — GOLD	3-582118-9
	NYLON 6/6; GRAY	BRASS — GOLD	3-582118-8
	NYLON 6/6; VIOLET	BRASS — GOLD	3-582118-7
	NYLON 6/6; BLUE	BRASS — GOLD	3-582118-6
	NYLON 6/6; GREEN	BRASS — GOLD	3-582118-5
OBSOLETE	NYLON 6/6; YELLOW	BRASS — GOLD	3-582118-4
	NYLON 6/6; ORANGE	BRASS — GOLD	3-582118-3
	NYLON 6/6; RED	BRASS — GOLD	3-582118-2
	NYLON 6/6; BROWN	BRASS — GOLD	3-582118-1
	NYLON 6/6; BLACK	BRASS — GOLD	3-582118-0
OBSOLETE	NYLON 6/6; WHITE	BRASS — SILVER	2-582118-9
	NYLON 6/6; GRAY	BRASS — SILVER	2-582118-8
	NYLON 6/6; VIOLET	BRASS — SILVER	2-582118-7
	NYLON 6/6; BLUE	BRASS — SILVER	2-582118-6
	NYLON 6/6; GREEN	BRASS — SILVER	2-582118-5
OBSOLETE	NYLON 6/6; YELLOW	BRASS — SILVER	2-582118-4
	NYLON 6/6; ORANGE	BRASS — SILVER	2-582118-3
	NYLON 6/6; RED	BRASS — SILVER	2-582118-2
	NYLON 6/6; BROWN	BRASS — SILVER	2-582118-1
	NYLON 6/6; BLACK	BRASS — SILVER	2-582118-0
OBSOLETE	NYLON 6/6; WHITE	BRASS — TIN	1-582118-9
	NYLON 6/6; GRAY	BRASS — TIN	1-582118-8
	NYLON 6/6; VIOLET	BRASS — TIN	1-582118-7
	NYLON 6/6; BLUE	BRASS — TIN	1-582118-6
	NYLON 6/6; GREEN	BRASS — TIN	1-582118-5
OBSOLETE	NYLON 6/6; YELLOW	BRASS — TIN	1-582118-4
	NYLON 6/6; ORANGE	BRASS — TIN	1-582118-3
	NYLON 6/6; RED	BRASS — TIN	1-582118-2
	NYLON 6/6; BROWN	BRASS — TIN	1-582118-1
	NYLON 6/6; BLACK	BRASS — TIN	1-582118-0

HOUSING — MATERIAL; COLOR		RECEPTACLE — MATERIAL; FINISH		PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 13APR2004	TE Connectivity	
DIMENSIONS: mm		CHK E. HOWARD 13APR2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .015 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD E. HOWARD 13APR2004	NAME ASSEMBLY, TEST PROBE	
MATERIAL SEE TABLE		FINISH SEE TABLE	SIZE A2	
		WEIGHT -	CAGE CODE 00779	DRAWING NO C=582118
		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE 6:1	SHEET 1 of 1	REV AB3

	—	—	—
	—	—	—
	—	—	—
	NYLON 6/6; NATURAL	BRASS — GOLD	6-582118-9
OBSOLETE	NYLON 6/6; NATURAL	BRASS — SILVER	5-582118-9
	HOUSING — MATERIAL; COLOR	RECEPTACLE — MATERIAL; FINISH	PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-582118-5](#)