







LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	A	INITIAL RELEASE		13JUN2019	AJ	SH	



2342933-1 AS SHOWN
SCALE 3:1



2342933-1 AS SHOWN
SCALE 4:1




DETAIL A
SCALE 8:1

1. MATERIAL:
CAGE MATERIAL : 0.25 THICK STAINLESS STEEL.
SPRING MATERIAL: COPPER ALLOY
CLIP MATERIAL: STAINLESS STEEL
HEAT SINK: ALUMINUM
2. FINISH:
SPRING: NICKEL PLATING
HEAT SINK: BLACK ANODIZATION
3. DIMENSION APPLIES WITH MODULE INSTALLED IN THE CAGE TO TOP OF HEAT SINK.
4. REFERENCE APPLICATION SPEC 114-60025 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
5. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.
6. MINIMUM PC BOARD THICKNESS : SINGLES SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN
7. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
8. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN
9. MATES WITH QSFP DD MSA COMPATIBLE TRANSCEIVER.


23.00	2	NETWORKING	2342933-3
16.00	2	SAN	2342933-2
13.70	2	PCI	2342933-1
DIM A	# REAR PINS	APPLICATION (HEAT SINK OPTION)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 29AUG2018	TE Connectivity	
		CHK: SEAN HAN 29AUG2018		
DIMENSIONS:		APVD: SEAN HAN 29AUG2018	NAME: CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
mm		PRODUCT SPEC		
		108-60122	SIZE: A1	
		APPLICATION SPEC		
		114-60025	SCALE: 2:1	
		FINISH		
MATERIAL: -		WEIGHT: -	SHEET 1 OF 5	
		CUSTOMER DRAWING	REV A	


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
		SEE SHEET 1		-	-	-	



2342933-1 AS SHOWN
WITH PCI HEAT SINK
SCALE 4:1



2342933-2 AS SHOWN
WITH SAN HEAT SINK
SCALE 4:1



2342933-3 AS SHOWN
WITH NETWORKING HEAT SINK
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: ARTHUR JIN 29AUG2018

CHK: SEAN HAN 29AUG2018

APVD: SEAN HAN 29AUG2018

DIMENSTONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.25

1 PLC ±0.25

2 PLC ±0.20

3 PLC ±0.10

4 PLC ±

ANGLES ±°

FINISH

PRODUCT SPEC

108-60122

APPLICATION SPEC

114-60025

WEIGHT

CUSTOMER DRAWING

NAME

CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER

SIZE

A1

CAGE CODE

-

DRAWING NO

©=2342933

RESTRICTED TO

-

SCALE

2:1

SHEET

2





OF

5


REV

A


LOC		DIST		REVISIONS				
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		-		SEE SHEET 1	-	-	-	





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 29AUG2018	TE Connectivity	
		CHK: SEAN HAN 29AUG2018		
DIMENSIONS:		APVD: SEAN HAN 29AUG2018	NAME	
mm		PRODUCT SPEC	CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER	
		108-60122	SIZE	
		APPLICATION SPEC	A1	
		114-60025	CAGE CODE	
		WEIGHT	2342933	
MATERIAL		CUSTOMER DRAWING	RESTRICTED TO	
			SCALE 2:1	
			SHEET 3 OF 5	
			REV A	



LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	29AUG2018	 TE Connectivity			
		CHK	29AUG2018				
DIMENSIONS:		SEAN HAN	29AUG2018	NAME			
mm		APVD	29AUG2018	CAGE ASSEMBLY, QSFP-DD STANDARD WITH EMI SPRING FINGER			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SIZE	
		0 PLC ±0.25		108-60122		CAGE CODE	
		1 PLC ±0.25		APPLICATION SPEC		DRAWING NO	
		2 PLC ±0.20		114-60025		REV	
MATERIAL		FINISH		WEIGHT		SCALE	
-		-		-		2:1	
				CUSTOMER DRAWING		SHEET 4 OF 5	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARTHUR JIN 29AUG2018		 TE Connectivity			
		CHK SEAN HAN 29AUG2018					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAGE ASSEMBLY, OSFP-DD STANDARD WITH EMI SPRING FINGER			
mm		0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.20 3 PLC ± 0.10 4 PLC $\pm .$					
		ANGLES FINISH		PRODUCT SPEC 108-60122 APPLICATION SPEC 114-60025			
MATERIAL				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		A1	-	C=2342933	-
CUSTOMER DRAWING				SCALE	2:1	SHEET	5 OF 5
				REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2342933-1](#)