








LOC	DIST	REVISIONS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		A	INITIAL	05DEC2018	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

AS SHOWN : I-2348454-0 (20POS:X-KEY)
ONLY 4POS---SEE SHEET 2 OF 3


20	X	9	22.5	26.0	27.6	I-2348454-0
16	X	7	17.5	21.0	22.6	I-2348454-8
12	X	5	12.5	16.0	17.6	I-2348454-6
10	X	4	10.0	13.5	15.1	I-2348454-5
8	X	3	7.5	11.0	12.6	I-2348454-4
6	X	2	5.0	8.5	10.1	I-2348454-3
4	X	1	2.5	6.0	7.6	I-2348454-2
POS	KEY	n	A	B	C	PART NO

1.MATERIAL:HOUSING:GLASS FIBER THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

2.FINISH(ALL OVER):NICKEL PL. 1.27µmMIN


3.FINISH(CONTACT OVER):TIN PL. 1.0µmMIN AFTER 2

4.THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER, ZHU 05DEC2018		TE Connectivity					
		CHK RICK, BIAN 05DEC2018							
		APVD RICK, BIAN 05DEC2018							
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5°		NAME 名称 DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS					
		0-PLC ±							
		1-PLC ±0.3							
		2-PLC ±0.10							
		3-PLC ±0.001							
		4-PLC ±0.0001		SIZE CAGE CODE DRAWING NO 番号 RESTRICTED TO					
		ANGLES ±							
MATERIAL 材料 &material		FINISH 仕上 -		A300779C-2348454					
		WEIGHT -		RESTRICTED CUSTOMER					
				SCALE 尺度 4:1		SHEET 1 OF 3		REV A	





THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1 OF 3		









RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : $1.0 \sim 1.6 \pm 0.1$

ONLY 4POS



SCALE 2:1

4POS(X-KEY):1-2348454-2












6POS(X-KEY):1-2348454-3

8POS(X-KEY):1-2348454-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER.ZHU 05DEC2018	 TE Connectivity			
DIMENSIONS: mm		CHK RICK.BIAN 05DEC2018				
		APVD RICK.BIAN 05DEC2018	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS			
		PRODUCT SPEC 108-78298	SIZE A3			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.3 1 PLC ± 0.10 2 PLC ± 0.10 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES $\pm$		APPLICATION SPEC 114-5377	CAGE CODE 00779			
MATERIAL &material		FINISH -	DRAWING NO C-2348454			
		WEIGHT -	RESTRICTED TO			
		RESTRICTED CUSTOMER	SCALE 4:1 SHEET 2 OF 3 REV A			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-			SEE SHEET 1 OF 3			



10POS(X-KEY):1-2348454-5

12POS(X-KEY):1-2348454-6

16POS(X-KEY):1-2348454-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL &material

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.3
1 PLC	±0.10
2 PLC	±0.10
3 PLC	±0.001
4 PLC	±0.0001
ANGLES	±0.001
FINISH	-

DWN FISHER.ZHU 05DEC2018

CHK RICK.BIAN 05DEC2018

APVD RICK.BIAN 05DEC2018

PRODUCT SPEC 108-78298

APPLICATION SPEC 114-5377

WEIGHT -

RESTRICTED CUSTOMER

TE Connectivity

NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS

SIZE A3	CAGE CODE 00779	DRAWING NO C-2348454	RESTRICTED TO
SCALE 4:1	SHEET 3 OF 3	REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2348454-8](#)