



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-18-002821	26FEB2018	KH	NN



Dimensions in mm [inches for reference]

Part No.	To Fit Connector Size	H		J		K		P REF b	R REF b	S REF b	U		W ±20% b	X ±20% b
		MIN a	MAX b	MIN a	MAX b	MIN a	MAX b				MIN a	±20% b		
234A011-XXC-0	9 WAY	20.8 [.82]	20.3 [.80]	15.7 [.62]	10.7 [.42]	9.0 [.35]	4.1 [.16]	26.0 [1.02]	22.0 [.87]	15.0 [.59]	3.0 [.12]	4.6 [.18]	1.0 [.04]	3.0 [.12]
234A021-XXC-0	15 WAY	29.0 [1.14]	28.2 [1.11]	15.7 [.62]	10.7 [.42]	11.0 [.43]	5.3 [.21]	31.0 [1.22]	25.0 [.98]	19.0 [.75]	3.8 [.15]	6.5 [.26]	1.0 [.04]	3.0 [.12]
234A032-XXC-0	25 WAY	42.8 [1.69]	42.2 [1.66]	15.7 [.62]	10.7 [.42]	15.0 [.59]	8.1 [.32]	43.0 [1.69]	28.0 [1.10]	22.0 [.87]	5.0 [.20]	7.5 [.30]	1.0 [.04]	3.0 [.12]
234A036-XXC-0	50 WAY	61.0 [2.40]	55.1 [2.17]	14.0 [.55]	10.7 [.42]	20.0 [.78]	10.6 [.41]	53.0 [2.08]	39.0 [1.53]	33.0 [1.30]	5.0 [.20]	10.0 [.39]	1.0 [.04]	3.0 [.12]
234A042-XXC-0	37 WAY	59.5 [2.34]	58.7 [2.31]	15.0 [.59]	10.7 [.42]	19.0 [.75]	8.6 [.34]	53.0 [2.08]	30 [1.18]	25.0 [.98]	6.0 [.24]	10.0 [.39]	1.0 [.04]	3.0 [.12]
234A052-XXC-0	50 WAY	57.5 [2.26]	57.9 [2.28]	16.5 [.65]	13.7 [.54]	19.0 [.75]	10.7 [.42]	56.0 [2.20]	32.0 [1.26]	25.0 [.98]	6.0 [.24]	10.0 [.39]	1.0 [.04]	3.0 [.12]

DIMENSIONS:

mm [INCHES]

DWN

P. VU

05JUL2017

MATERIAL

-

FINISH

-

CHK

N, NAGAR

05JUL2017

APVD

A. POOLE

05JUL2017

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

NAME

RIGHT ANGLED BOOT, RECTANGULAR SUBMINIATURE, COATED

234A0XX-XXC-0

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-

234A0XX-XXC-0

-

CUSTOMER DRAWING


SCALE

DNS

SHEET

1 OF 2

REV A



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By TE Connectivity

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash Number	Material Description	SPEC No.	Coating Slash No.
-25C	ELASTOMER/SILVER COMPOSITE	RW-3047	/86, /200

ORDERING INFORMATION

234A0**--**C/**-0



NOTES

- As supplied dimensions are for parts without adhesive, when an adhesive layer is added entry diameters will reduce by 1.5mm Max.


IT IS ESSENTIAL THAT THESE PARTS ARE INSTALLED ON THE CONNECTOR WITH THE APPROPRIATE INSTALLATION CLAMPING TOOL. THIS ENSURES GOOD CONTACT BETWEEN THE BOOT AND CONNECTOR. THE RECOMMENDED CLAMP PART NUMBER IS :- AT-7-031 TIN PLATED CONNECTORS ARE RECOMMENDED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By TE Connectivity

DIMENSIONS: mm [INCHES]		DWN P. VU	05JUL2017	MATERIAL —	FINISH —
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK N, NAGAR	05JUL2017	 TE Connectivity	
		APVD A. POOLE	05JUL2017		
		PRODUCT SPEC —		NAME RIGHT ANGLED BOOT, RECTANGULAR SUBMINIATURE, COATED 234A0XX-XXC-0	
		APPLICATION SPEC —		SIZE A4	CAGE CODE 00779
WEIGHT		CUSTOMER DRAWING			
		SCALE DNS		SHEET 2 of 2	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EM3691-000](#)