


LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	REVISED PER ECR-20-000721	04MAR2020	PC	SW

The worksheet is divided into two main sections. The top section is a tracing guide for the letter 'A'. It shows a large uppercase 'A' and a smaller lowercase 'a'. A triangle with the number '4' is positioned above the uppercase 'A', with an arrow pointing to a small square on the letter, indicating a specific point of interest or a step in the tracing process. Below the tracing guide is a wavy line separating it from the bottom section. The bottom section is a cutting practice area. It contains three large uppercase 'A's and three large lowercase 'a's, each followed by a small square. To the right of these letters are three rectangular boxes, each containing a horizontal line. The entire cutting practice area is bounded by a wavy line at the top and a straight line at the bottom.



2. CONTACTS ACCEPT 24 AWG WIRE WITH 1.52[.060] MAX INSULATION DIAMETER.
3. CONTACTS MUST ACCEPT 0.64±0.03[.025] POST AND REMAIN LOCKED IN POSITION.
4. IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
5. DIMENSIONS IN BRACKETS ARE IN INCHES.
6. HOUSING FEATURES ARE: FEED THRU WITH LOCKING RAMP AND WITH POLARIZING TAB.

8 PRELIMINARY - NOT FOR PRODUCTION FOR 6-644563-2 THRU 8-644563-4.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 12JUN2003		 TE Connectivity	
		CHK D. BOSSI 12JUN2003			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-100 CONNECTOR ASSEMBLY, 24 AWG, STANDARD	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.13 [.005] 4 PLC ± ANGLES ±			
MATERIAL		FINISH			
					
		APVD D. BOSSI 12JUN2003		RESTRICTED TO	
		PRODUCT SPEC 108-1050			
		APPLICATION SPEC 114-1019			
		WEIGHT		A2	
				00779	
				C-644563	
		CUSTOMER DRAWING		SCALE 5:1	
				SHEET 1 OF 1	
				REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-644563-8](#)