



LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			T	REVISED PER ECO-12-012320	04JUL12	KH	MZ

- 1
- 0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm[.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 2
- 1.27um [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76um [.000030] MIN NICKEL PER QQ-N-290.
- 3
- 0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25μm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 4
- 0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm[.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 5
- 1.27μm [.000050] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH GOLD FLASH ON REMAINDER OVER 1.90μm [.000075] MIN NICKEL PER QQ-N-290.
- 6
- GOLD PLATING NEED NOT APPEAR IN THIS AREA EXCEPT 66424-9 HAS GOLD PLATING ON INSULATION BARREL.
- 7
- REVERSE REELED FOR MINI-APPLICATOR.
8.
- WIRE RANGE 26-30 AWG.
INSULATION RANGE 1.02[.040]-1.52[.060].
- 9
- 0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27μm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27μm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 10
- 1.27um [.000050] MIN TIN PER MIL-T-10727 OVER 0.76um [.000030] MIN NICKEL PER QQ-N-290.
- 11
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	<div>7</div>	<div>10</div>	-	1-66424-1
OBSOLETE	<div>7</div>	<div>9</div>	66428-5	1-66424-0
OBSOLETE	<div>7</div>	<div>5</div>	-	66424-9
	<div>7</div>	<div>1</div>	66428-4	66424-8
	<div>7</div>	<div>4</div>	66428-3	66424-7
	<div>7</div>	<div>2</div>	-	66424-6
OBSOLETE	<div>7</div>	<div>3</div>	66428-1	<div>11</div> 66424-5
	STANDARD	<div>4</div>	66428-3	66424-3
OBSOLETE	STANDARD	<div>3</div>	66428-1	66424-1
	REELING	BODY FINISH	LOOSE PIECE REF	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	08/06/91	<div> TE Connectivity</div>		
		CHK	9-19-91			
DIMENSIONS: mm [INCHES]		APVD	-	NAME SOCKET ASSEMBLY, .062, TYPE III+		
<div></div>		PRODUCT SPEC	-			
		APPLICATION SPEC	-			
MATERIAL SEE CALLOUTS		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
		FINISH		A2	00779	C=66424
		SEE CALLOUTS		CUSTOMER DRAWING		RESTRICTED TO
				SCALE	SHEET	REV
				8:1	1 of 1	T

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66424-8](#)